

TRONEX

7212 - Medium Taper Flush Cutter



- **Application:** Used for general purpose cutting, strong and versatile.
- **Head Shape:** Medium Taper Head
- **Profile:** Standard
- **Material:** Carbon Steel
- **Material Hardness:** 62-63 HRC
- **Cutting Edge:** Flush
- **Cutting Capacity (soft copper wire):** .006" - .049" (.15mm – 1.25mm); 35-16 AWG
- **Handle Length:** Long Ergonomic
- **Handle Grips:** Cushion Double Sheathed, ESD Safe

- **RTT Resistance:** $<1 \times 10^{11}$ ohms tested per ANSI/ESD STM11.13 Two-Point Probe, resistance measurement for static dissipative materials
- **Overall Length:** 5.6" (142mm)