



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: Hood

Cable Entry Location: Top & Side

Features

Product Type Features

|                                    |      |
|------------------------------------|------|
| Hood & Base Connector Product Type | Hood |
|------------------------------------|------|

Body Features

|                      |                   |
|----------------------|-------------------|
| Material             | Die Cast Aluminum |
| Color                | Gray              |
| Cable Entry Location | Top & Side        |

Mechanical Attachment

|                          |         |
|--------------------------|---------|
| Locking Device Location  | Housing |
| Screw & Hole Thread Size | M20     |

Usage Conditions

|                     |     |
|---------------------|-----|
| Corrosion Protected | Yes |
|---------------------|-----|

Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Quantity | 1   |
| Packaging Method   | Bag |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                             |
|-----------------------------------------------|---------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                   |
| EU ELV Directive 2000/53/EC                   | Compliant                                   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold     |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211) |



Candidate List Declared Against: JAN 2020  
(205)  
SVHC > Threshold:  
Not Yet Reviewed

|                           |                                            |
|---------------------------|--------------------------------------------|
| Halogen Content           | Not Yet Reviewed for halogen content       |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1509161000-000  
H16A-AGS



TE Part # T3609200102-000  
DLX-20-M



TE Part # T2010162101-000  
HA-016-M



TE Part # T1019161201-001  
H16A-KDTMS


Also in the Series | HDC IP65



Rectangular Connector Hoods & Bases  
(1258)

Customers Also Bought





TE Part #1-281786-2  
HE13/HE14 IDC Receptacle, SRST, AWG24-2



TE Part #2273076-3  
M12 A-CODE MALE R/A PIGTAIL




TE Part #EC0372-000  
Z-TYPE PUSH-ON MARKERS



TE Part #1558676-6  
PCB Power Relay: 30 amp, Monostable DC



TE Part #1-282858-2  
12P. TERMI-BLOK PCB MOUNT 90



TE Part #1-292499-4  
SLIDE LOCK PANEL MT CBL HSG 5HDP



TE Part #2-2364570-8  
AVH19 FLT SS LK RNG R&B 24V16A



TE Part #2-2364686-4  
AVH22 FLT SS LK RNG R&G 24V16A



TE Part #1-2364686-5  
AVH22 FLT SS MT RNG GRN 24V16A



TE Part #2176415-4  
8W STD M/OX 5% 39R

Documents

Product Drawings

H16A-TGH-M20

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_T1349160120-000\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1349160120-000\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1349160120-000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages





HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Application Specification