



## Product Change Notification / KSRA-13AKNI696

---

### Date:

26-Feb-2021

### Product Category:

8-bit Microcontrollers, Capacitive Touch Sensors, Touch Controllers

### PCN Type:

Manufacturing Change

### Notification Subject:

CCB 4440 Final Notice: Qualification of MMT as an additional assembly site for selected MTCH112, MTCH810 and PIC12xxxx device families available in 8L DFN (3x3x0.9mm) package.

### Affected CPNs:

[KSRA-13AKNI696\\_Affected\\_CPN\\_02262021.pdf](#)

[KSRA-13AKNI696\\_Affected\\_CPN\\_02262021.csv](#)

### Notification Text:

**PCN Status:**Final notification

**PCN Type:**Manufacturing Change

**Microchip Parts Affected:**Please open one of the icons found in the Affected CPNs section.

NOTE: For your convenience Microchip includes identical files in two formats (.pdf and .xls).

**Description of Change:**Qualification of MMT as an additional assembly site for selected MTCH112, MTCH810 and PIC12xxxx device families available in 8L DFN (3x3x0.9mm) package.

#### Pre Change:

Assembled at NSEB using gold (Au) or palladium coated copper wire with gold flash (CuPdAu) bond wire, 8600 die attach material, EFTEC-64T lead frame or C194 lead frame material, Ag DAP surface prep or Bare Cu DAP surface prep and without lead lock lead frame

#### Post Change:

Assembled at NSEB using gold (Au) or palladium coated copper wire with gold flash (CuPdAu) bond wire, 8600 die attach

material, EFTEC-64T lead frame or C194 lead frame material, Ag DAP surface prep or Bare Cu DAP surface prep and without lead lock lead frame

or

Assembled at MMT using palladium coated copper wire with gold flash (CuPdAu) bond wire, 3280 die attach material, C194 lead frame material and Bare Cu DAP surface prep and with lead lock lead frame.

#### Pre and Post Change Summary:

	Pre Change		Post Change		
Assembly Site	UTAC Thai Limited LTD. (NSEB)		UTAC Thai Limited LTD. (NSEB)		Microchip Technology Thailand (Branch) / MMT
Wire material	Au	CuPdAu	Au	CuPdAu	CuPdAu
Die attach material	8600		8600		3280
Molding compound material	G700LTD		G700LTD		G700LTD
Lead frame material	EFTEC-64T	C194	EFTEC-64T	C194	C194
Lead Frame DAP Surface Prep	Ag	Bare Cu	Ag	Bare Cu	Bare Cu
Lead frame lead-lock	No		No		Yes
	See Pre and Post Change attachment for lead frame comparison				

**Impacts to Data Sheet:**None.

**Change Impact:**None.

**Reason for Change:**To improve on-time delivery performance by qualifying MMT as an additional assembly site.

**Change Implementation Status:**In Progress

#### Estimated First Ship Date:

February 10, 2021 (date code: 2107)

NOTE: Please be advised that after the estimated first ship date customers may receive pre and post change parts.

#### Time Table Summary:

	November 2020					→	January 2021					February 2021			
Workweek	45	46	47	48	49		01	02	03	04	05	06	07	08	09
Initial PCN Issue Date			X												
Final PCN Issue Date											X				
Qual Report Availability															X
Estimated First Ship Date													X		

**Method to Identify Change:**Traceability code

### Qualification Report:

Please open the attachments included with this PCN labeled as PCN\_#\_Qual\_Report.

**Revision History:****November 20, 2020:** Issued initial notification.**January 29, 2021:** Issued final notification. Provided estimated first ship date to be February 10, 2021.**February 26, 2021:** Reissued final notification. Included qual report attachment and updated qual report availability.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

### Attachments:

[PCN\\_KSRA-13AKNI696\\_Pre\\_and\\_Post Change Summary.pdf](#)  
[PCN\\_KSRA-13AKNI696 Qual Report.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

### Terms and Conditions:

If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.

Affected Catalog Part Numbers (CPN)

PIC12F1822-E/MF  
PIC12F1822-I/MF043  
PIC12F1822-I/MF  
PIC12F1822T-I/MF  
PIC12F1822T-E/MF  
PIC12LF1822-E/MF  
PIC12LF1822-I/MF  
PIC12LF1822T-I/MF  
PIC12F1840-E/MF  
MTCH810-I/MF  
PIC12F1840-I/MF  
PIC12F1840-H/MF  
MTCH810T-I/MF  
PIC12F1840T-I/MF  
PIC12F1840T-E/MF  
PIC12LF1840-E/MF  
MTCH112-I/MF  
PIC12LF1840-I/MF  
MTCH112T-I/MF  
PIC12LF1840T-I/MF  
PIC12F1501-E/MF  
PIC12F1501-I/MF  
PIC12F1501T-E/MF  
PIC12LF1501-E/MF  
PIC12LF1501-I/MF  
PIC12F1612-I/MF  
PIC12LF1612-E/MF  
PIC12F1571-E/MF  
PIC12F1572-E/MF  
PIC12F1571-I/MF059  
PIC12F1571-I/MF  
PIC12F1572-I/MF  
PIC12F1571T-I/MF059  
PIC12F1571T-I/MF  
PIC12F1572T-I/MF  
PIC12F1571T-E/MF  
PIC12F1572T-E/MF  
PIC12LF1571-E/MF  
PIC12LF1572-E/MF  
PIC12LF1571-I/MF  
PIC12LF1572-I/MF  
PIC12LF1572T-I/MF  
PIC12LF1572T-I/MFSIS



## **QUALIFICATION REPORT SUMMARY**

**PCN#: KSRA-13AKNI696**

Date  
February 04, 2021

Qualification of MMT as an additional assembly site for selected MTCH112, MTCH810 and PIC12xxxx device families available in 8L DFN (3x3x0.9mm) package.



## **MICROCHIP**

### **PACKAGE QUALIFICATION REPORT**

<b>Purpose</b>	Qualification of MMT as an additional assembly site for selected MTCH112, MTCH810 and PIC12xxxx device families available in 8L DFN (3x3x0.9mm) package.
<b>CCB No</b>	4440
<b>CN</b>	ES349377
<b>QUAL ID</b>	R2000923 Rev. B
<b>MP CODE</b>	LEBD24A7XB04
<b>Part No.</b>	PIC12F1822-E/MF
<b>Bonding No.</b>	BDM-002698 Rev. A
<b><u>Package</u></b>	
<b>Type</b>	8L DFN
<b>Package size</b>	3 x 3 x 0.9 mm
<b><u>Lead Frame</u></b>	
<b>Paddle size</b>	102 x 71 mils
<b>Material</b>	C194
<b>Surface</b>	Bear Cu
<b>Process</b>	BOT
<b>Lead Lock</b>	Yes
<b>Part Number</b>	10100851
<b><u>Material</u></b>	
<b>Epoxy</b>	3280
<b>Wire</b>	CuPdAu wire
<b>Mold Compound</b>	G700LTD
<b>Plating Composition</b>	Matte Sn



# **MICROCHIP**

## **PACKAGE QUALIFICATION REPORT**

### **Manufacturing Information**

<b>Assembly Lot No.</b>	<b>Wafer Lot No.</b>	<b>Date Code</b>
MMT-213201463.000	TMPE221064499.400	204562M
MMT-213301391.000	TMPE221064499.400	2046GUK
MMT-213202606.000	TMPE221064499.400	2045GUJ

### **Result**

☒ Pass ☐ Fail ☐ \_\_\_\_\_

8L DFN (3x3x0.9 mm) assembled by MMT pass reliability test per QCI-39000. This package was qualified the Moisture/Reflow Sensitivity Classification Level 1 at 260°C reflow temperature per IPC/JEDEC J-STD-020E standard.

## PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS	Result	Remarks
<b><u>Precondition</u></b> <b><u>Prior Perform</u></b> <b><u>Reliability Tests</u></b> <b>(At MSL Level 1)</b>	<b>Electrical Test:</b> +25°C, 85°C and 125°C System: J750	JESD22-A113	693(0)	693		Good Devices
	Bake 150°C, 24 hrs System: CHINEE	JIP/IPC/JEDEC J-STD-020E		693		
	85°C/85%RH Moisture Soak 168 hrs. System: TABAI ESPEC Model PR-3SPH			693		
	3x Convection-Reflow 265°C max  System: Vitronics Soltec MR1243			693		
	<b>Electrical Test:</b> +25°C, 85°C and 125°C System: J750			0/693	Pass	



# PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks
<b>Temp Cycle</b>	<b>Stress Condition:</b> -65°C to +150°C, 500 Cycles System: TABAI ESPEC TSA-70H <b>Electrical Test:</b> + 85°C and 125°C System: J750 <b>Stress Condition:</b> -65°C to +150°C, 1000 Cycles System: TABAI ESPEC TSA-70H <b>Electrical Test:</b> +85°C and 125°C System: J750 <b>Bond Strength:</b> Wire Pull (> 2.5 grams) Bond Shear (>15.00 grams)	JESD22-A104		231		Parts had been pre-conditioned at 260°C 77 units / lot
			231(0)	0/231	Pass	
				231		
			231(0)	0/231	Pass	
			15 (0)	0/15	Pass	
			15 (0)	0/15	Pass	
<b>UNBIASED-HAST</b>	<b>Stress Condition:</b> +130°C/85%RH, 96 hrs. System: HAST 6000X <b>Electrical Test:</b> +25°C System: J750 <b>Stress Condition:</b> +130°C/85%RH, 192 hrs. System: HAST 6000X <b>Electrical Test:</b> +25°C System: J750	JESD22-A118		231		Parts had been pre-conditioned at 260°C 77 units / lot
			231(0)	0/231	Pass	
				231		
			231(0)	0/231	Pass	
<b>HAST</b>	<b>Stress Condition:</b> +130°C/85%RH, 96 hrs. <b>Bias Volt:</b> 5.0 Volts System: HAST 6000X <b>Electrical Test:</b> + 25°C ,85°C and 125°C System: J750 <b>Stress Condition:</b> +130°C/85%RH,192 hrs. <b>Bias Volt:</b> 5.0 Volts System: HAST 6000X <b>Electrical Test:</b> + 25°C ,85°C and 125°C System: J750	JESD22-A110		231		Parts had been pre-conditioned at 260°C 77 units / lot
			231(0)	0/231	Pass	
				231		
			231(0)	0/231	Pass	

## PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks
<b>High Temperature Storage Life</b>	<b>Stress Condition:</b> Bake 175°C, 504 hrs System: SHEL LAB	JESD22- A103		45		45 units
	<b>Electrical Test:</b> +25°C, 85°C and 125°C System: J750		45(0)	0/45	Pass	
<b>Wire sweep</b>	Wire sweep Inspection 15 Wires / lot	-	45(0) Wires	0/45	Pass	
<b>Bond Strength Data Assembly</b>	Wire Pull (> 2.5 grams)	Mil.Std. 883-2011	30 (0) Wires	0/30	Pass	
	Bond Shear (>15.00 grams)	CDF-AEC- Q100-001	30 (0) bonds	0/30	Pass	

**CCB 4440**  
**Pre and Post Change Summary**  
**Lead Frame Comparison**  
**PCN#: KSRA-13AKNI696**



---



A Leading Provider of Smart, Connected and Secure Embedded Control Solutions



SMART | CONNECTED | SECURE

# Lead frame comparison

8L DFN (3x3x0.9mm)

Pre change	Post Change				
NSEB	MMT				
 <p>The diagram shows two lead frame layouts for NSEB. The left layout is labeled 'NSEB : FR0230' and features a central square cavity with a textured pattern. The right layout is labeled 'NSEB : FR1347' and is a solid rectangular frame. Both layouts have eight leads, numbered 1 through 8, arranged in two columns of four on each side.</p>	 <p>The diagram shows a lead frame layout for MMT, labeled 'MMT : 10100851'. It is a solid rectangular frame with eight leads, numbered 1 through 8, arranged in two columns of four on each side.</p>				
<table><tr><td>Lead frame lead-lock</td><td>No</td></tr></table>	Lead frame lead-lock	No	<table><tr><td>Lead frame lead-lock</td><td>Yes</td></tr></table>	Lead frame lead-lock	Yes
Lead frame lead-lock	No				
Lead frame lead-lock	Yes				