



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

### Features

#### Product Type Features

|                                    |      |
|------------------------------------|------|
| Product Size                       | 7    |
| Hood & Base Connector Product Type | Hood |

#### Body Features

|                      |                   |
|----------------------|-------------------|
| Material             | Die Cast Aluminum |
| Color                | Gray              |
| Cable Entry Location | Side              |

#### Mechanical Attachment

|                          |         |
|--------------------------|---------|
| Locking Device Location  | Housing |
| Screw & Hole Thread Size | M25     |

#### Usage Conditions

|                     |     |
|---------------------|-----|
| Corrosion Protected | Yes |
|---------------------|-----|

#### Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Quantity | 1   |
| Packaging Method   | Bag |

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant                               |
| EU ELV Directive 2000/53/EC                   | Compliant                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021  
 (211)  
 Candidate List Declared Against: JAN 2021  
 (211)  
 Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # T2010162201-000  
HA-016-F



TE Part # T3609250102-000  
DLX-25-M



TE Part # T1319320125-000  
H32A-TS-M25



TE Part # T2010322201-000  
HA-016-F 17-32

## Also in the Series | HDC IP65



Rectangular Connector Hoods & Bases  
(1258)

## Customers Also Bought



## Documents

### Product Drawings

H32A-SGR-M25

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T1449320125-000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1449320125-000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1449320125-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



[Heavy Duty Connectors](#)

English

[HEAVY DUTY CONNECTORS](#)

English

---

[Product Specifications](#)

[Application Specification](#)

English

[Application Specification](#)