



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

Circuit Application: **Power & Signal**

Features

Product Type Features

Product Size	4
Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Material	Die Cast Aluminum
Cable Entry Location	Bottom

Mechanical Attachment

Locking Device Location	Housing
Screw & Hole Thread Size	2PG21
Hood & Base Locking Device Type	Locking

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1250102125-000
H10B-TSB-M25



TE Part # T2040102201-000
HE-010-F



TE Part # T3609250102-000
DLX-25-M


Also in the Series | HDC IP65




Rectangular Connector Hoods & Bases
(1258)




Customers Also Bought




TE Part #T1329031120-000
H3A-TG-M20




TE Part #T1230160129-000
H16B-TSH-PG29




TE Part #T1210240121-000
H24B-TS-PG21




TE Part #T1410162000-000
H16B-AG




TE Part #T1010032100-000
H3A-KDBP-NY150




TE Part #T1010102100-000
H10B-KDBP




TE Part #T1250102116-000
H10B-TSB-PG16



TE Part #T1270162129-000
H16B-TSBH-PG29



TE Part #T1270242129-000
H24B-TSBH-PG29



TE Part #T3209091201-000
HSK-P09G

Documents

Product Drawings

H10B-AD-BO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1430100000-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T1430100000-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T1430100000-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English