

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0908140506](#)
Status: **Active**
Overview: [Picoflex Ribbon-Cable Connectors](#)
Description: Picoflex PF-50 Header without PCB Pegs, Vertical, Standard Profile, Surface Mount, Tin (Sn) Plated, 6 Circuits, Tape and Reel, Natural

Documents:

[3D Model](#) [Product Specification PS-99020-0011-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E29179

Application tooling part link

Application Tooling Part Link 69008-1070

General

Product Family PCB Headers
 Series [90814](#)
 Application Signal, Wire-to-Board
 Comments Standard Profile
 Overview [Picoflex Ribbon-Cable Connectors](#)
 Product Name Picoflex
 UPC 756054850329

Physical

Breakaway No
 Circuits (Loaded) 6
 Circuits (maximum) 6
 Color - Resin Natural
 Durability (mating cycles max) 30
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Capable No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 0.500/g
 Number of Rows 1
 Orientation Vertical
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 1.27mm
 Pitch - Termination Interface 1.27mm
 Plating min - Mating 3.048µm
 Plating min - Termination 3.048µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Shrouded No
 Stackable No
 Surface Mount Compatible (SMC) N/A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90814](#) Series

Mates With

[90327](#) IDT Connector

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Picoflex PF-50 Connectors, 4-26 Circuits	690081070

Temperature Range - Operating
Termination Interface: Style

-40° to +105°C
Surface Mount

Electrical

Current - Maximum per Contact
Voltage - Maximum

2.4A
250V

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-99020-0011-001
908149002-000, SDA-90814-001

This document was generated on 03/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION