

ED-582 Ethernet to RTD

4 Channel RTD Input

- · 4 Channel RTD Inputs
- · Supports simple ASCII 1 Ethernet Port
- -30°C to +80°C/-22°F to +176°F
 Temperature range
- · Software APIs for VB, C# and more
















Non conducting polyamide casing with removable numbered terminal blocks for easy wiring



+5 to +30 Volt Power Input enables the device to be run from USB, a vehicle battery or the factory floor



Integral DIN mount and slim design takes up minimal cabinet space





















ED-582

Ethernet to RTD

Integrate with popular software packages or use with our free APIs

Supports ASCII commands

Integral DIN rail clip with earth

View from webpage - no software required

IP20 Non-conducting polyamide case with vents

Easy Wire Removable screw terminal blocks

4 channel RTD

Serial Expansion Port suitable for ADAM modules

Ethernet Port

-30°C to +80°C/-22°F to +176°F temperature range


Wide Range Input Power: +5VDC to +30VDC

Connectors				
Screw Terminals	3.5mm pitch			
Wire Thickness	#22 - #14, 0.5mm²-2.5mm²			
Power Supply	'			
Power Supply input	Unregulated +5V to +30Volts DC, reverse polarity protection			
Isolation	1500VRMS Magnetic isolation from Ethernet			
Environmental	'			
Operating Temperature	-30 ^o C to +80 ^o C / -22°F to +176°F			
Storage Temperature	-40 ^o C to +85 ^o C / -40°F to +185°F			
Ambient Relative Humidity	5 to 95% (non-condensing)			
Magjack LED Information	'			
Link/Activity LED	Solid green	Connection established		
	Flashing Green	Data communication		
Speed LED	Green	100Base-Tx		
	Unlit	10Base-T		
Ethernet				
Ethernet Port	RJ45 jack, 10/100Mhz autosensing, crossover auto sensing (Auto MDIX)			
Protection	1,500 Volts magnetic isolation between ports			
Housing	IP-20 rated non-conducting polyamide case			



ED-582

Ethernet to RTD



Terminal Block Pin Outs

Terminal Block	Pin 1	Pin 2	Pin 3	Pin 4	Pin 5
Grey	SIG GND	RS-485 D-	RS-485 D+	RS-485 D+	RS-485 D-
Black	-V	+VA	+VB	-V	Func GND
Power Input +5V to +30V DC 100mA@24V 2.5W Max					
Yellow	RTD Input 0	4-WIRE	3-W	/IRE	2-WIRE
Orange	RTD Input 1	1 2 3 4	5 1 2 T-	3 4 5 1 1	2 3 4 5
Green	RTD Input 2		}		
Blue	RTD Input 3				

Ethernet Port Pin Outs

PIN FUNCTION 1 RD+ / TD+ 2 RD- / TD- 3 TD+ / RD+ 4 NC 5 NC	
2 RD- / TD- 3 TD+ / RD+ 4 NC	PIN
3 TD+ / RD+ 4 NC	1
4 NC	2
	3
5 NC	4
	5
6 TD- / RD-	6
7 NC	7
8 NC	8

Lifetime Warranty and Support:

We can help with every aspect of your project, from getting you up and running to custom application.



ED-582

Ethernet to RTD

RTD Channels - 4 Inputs

Inputs

Inputs	
IO Protocols	DCON ASCII over TCP
Description	4 RTD sensor inputs - individually configurable for sensor type
Isolation	Yes, RTD inputs are isolated from the power, network and RS-485 ports
RTD types	Pt-100, Pt-1000, Ni-120
RTD connection	2, 3 or 4-wire connection
RTD Standards	IEC/EN 60751, JIS C1604-1987, US Industrial, International, RTD1000-375, Ni-120
Measurement range	-200°C - 600°C
Input Resolution	16 bit resolution
Measurement Accuracy	2/4 wire:- ±0.2°C with ED-582 at 25°C ±1.2°C with ED-582 at -30 to +80°C (NOTE: 2-wire mode accuracy will be affected by customer's choice of RTD cable connection) 3-wire:- ±0.5°C with ED-582 at 25°C ±1.2°C with ED-582 at -30 to +80°C
Measurement rate	5 measurements per second, divided between all enabled inputs
Low Noise	CMRR > 120dB
Rejects Mains Hum	NMRR > 75dB at 50Hz and 60Hz

Serial Expansion Port - RS485

Half Duplex RS485 port allows connection and control of industry standard NuDAM, eDAM and ADAM modules using ASCII protocols.

Power Supply

Power Supply input Unregulated +5V to +30Volts DC, reverse polarity protection

Isolation 1500VRMS Magnetic isolation from Ethernet

Power Consumption 2.5 Watts Max : 220 mAmps@+5VDC/36mAmps@+30VDC



Software

OS Compatibility Brainboxes' software provides a TCP or Serial COM port interface. All

software versions and updates available to download from our website.

Microsoft Windows 8, Windows 8.1, Windows 10

Windows Server 2016 Windows Server 2019

Other TCP and web browser interface for other OSs & Linux, e.g. Android,

Raspberry Pi















Boost.IO Manager

Lets you find, install and upgrade devices

Industry Standard Packages

The COM port based driver means devices are compatible with popular packages such as: LabView, MATLAB, Agilent VEE. So you can continue to get value from your existing development and process control system.

Software Platforms

APIs and sample program code for: Microsoft .NET, C#, Visual Basic, C++, JavaScript, PHP, Java, Objective-C, Python and more - www.brainboxes.com















ASCII

The ED device's webpage has an interactive ASCII console where any command can be entered and it is immediately executed showing the device's response.

\$01M	read the name of device address 01
!01ED-582	device 01 replies that its name is ED-582
\$01F	read firmware version number of device address 01
!012.54	firmware version of device 01 is 2.54

Full command tables can be found in the device manual









= [)-5	27	Ethernet to	RTD
	J- 7	\wedge		טוא

Packaging Information Installation CD including manual, Microsoft signed drivers & utilities,

Quick Start Guide, Device

Packaged Weight 0.225 kg, 7.94 ounces

Packaged Dims 160x135x49 mm, 6.3x5.3x1.9 inches

GTIN Universal Code 837324004021

Industry Approvals METLABS E112324 complies with UL60950-1, CSA C22.2, No. 60950-1

Microsoft Certified Gold Partner, WEEE, RoHS, AEO (C-TPAT), CE, UKCA

HTS 8517620000

ECCN 5A991.b

CAGE 8QCY6

Warranty Lifetime - online registration required

Support Lifetime Web, Email & Phone Support from fully qualified, friendly staff

who work in and alongside the Product Development Team

Standards ISO9001, ISO14001

OEM option Available for bulk buy OEM

COO (Country of Origin) GB

Made In Manufactured in GB by Brainboxes

Customisable Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users

More info:sales@brainboxes.com



ED Range

Remote I/O products available in a range of formats and specifications

www.brainboxes.com



PW-600

Power supply with connectors for UK, USA, EU and AUS mains socket. 'Tails' are suitable for connecting to screw terminal blocks.



PW-650

Power supply with USB connector and pre-wired screw terminal block. Suitable for use with 5V USB ports.



MK-588

6 coloured PCB connectors. Individually numbered pins; 5 x 3.5mm pitch screw connections with tension sleeve.

© Brainboxes 2021 BBEDI170419