Coaxial Cable

pro-**Power**

RoHS

Compliant



Specifications

Designed of cable	
Inner Conductor	: Solid bare copper 1/0.8 ±0.004mm
Insulation	: Foamed PE
Size of Insulation	: Ø3.7 ±0.1mm
Screening	: Bonded Foil
Braiding	: 16×3/0.12 ±0.003mm AL/MG
Inner conductor	: Stranded bare copper 24/0.15±0.004mm
Insulation	: PE
Size of Insulation	: Ø2.1 ±0.1mm
Colour	: Red/Black
Jacket	: PVC
Jacket Colour	: Black
Jacket Size	: Ø6 +5.8 ±0.2mm
Wall Thickness	: ≈0.8mm
Jacket Printing	: RG59 Power RW meter marking
Electric data at 20°C	
Conductor Resistance	: ≤38Ω/KM
Conductor Resistance	: ≤48Ω/KM
Insulation Resistance	: ≥5000MΩ*KM
Testing Voltage	: wire/wire 50Hz 1min=1.5KV
Impedance	: 75±3Ω at 200Mhz
ATT max less than 10%:	

 Frequency
 50
 100
 200
 800
 1000

 ATT dB/100m
 6.8
 9.5
 12.9
 23.5
 31

Temperature Range

: -10°C to +60°C

Part Number Table

Description	Part Number
Coaxial Cable, RG59, 25AWG, 0.15mm ² , 250m	RG59U+FLEX250M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

