

T1739032111-000 ✓ ACTIVE

HDC | HDC IP65

TE Internal #: T1739032111-000

TE Internal Description: H3A-TGVB-PG11

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Top & Side**

Features

Product Type Features

Product Size	1
Hood & Base Connector Product Type	Hood

Body Features

Material	Die Cast Aluminum
Color	Gray
Cable Entry Location	Top & Side

Mechanical Attachment

Locking Device Location	Housing
Screw & Hole Thread Size	PG11

Dimensions

Width	24 mm
Height	57 mm
Length	24 mm

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T2010032201-000
HA-003-F



TE Part # T1329031111-000
H3A-TG-PG11



TE Part # T3609110101-000
DLX-11-MS



TE Part # T1010032100-000
H3A-KDBP-NY150

Also in the Series | HDC IP65



Rectangular Connector Hoods & Bases
(1258)

Customers Also Bought



TE Part #281783-5
HE13/HE14 IDC Receptacle, SRST,
AWG24-2



TE Part #144273-5
HE13/HE14 IDC Receptacle, SRRA,
AWG24



TE Part #4-644467-1
11P MTA156 CONN ASSY 22AWG LF



TE Part #3-640426-4
04P MTA156 CONN ASSY 18AWG
ORA



TE Part #5-534237-2
04 MODII VRT SR CE 100/115



TE Part #4-1437662-8
BC6-T408-08=BC6 SERIES




TE Part #4-644467-0
10P MTA156 CONN ASSY 22AWG LF



TE Part #1-2329359-0
PB ON/OFF HC BLU M1 TERM IP68
500MM LHS



TE Part #3-1879351-5
RR01 5% 75K AMMO



TE Part #T4111002052-000
M12,MALE,STRAIGHT,A CODE,5P,
PG9,SILVER

Documents

Product Drawings

H3A-TGVB-PG11

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_T1739032111-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1739032111-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1739032111-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Application Specification