RGTV80TS65

650V 40A Field Stop Trench IGBT

Datasheet


V _{CES}	650V
I _{C (100°C)}	40A
V _{CE(sat) (Typ.)}	1.5V
P_{D}	234W

Outline TO-247N (1) (2)(3)

Features

- 1) Low Collector Emitter Saturation Voltage
- 2) High Speed Switching & Low Switching Loss
- 3) Short Circuit Withstand Time 2µs
- 4) Pb free Lead Plating; RoHS Compliant

●Inner Circuit



Application

Solar Inverter

UPS

Welding

ΙH

PFC

●Packaging Specifications

Tackaging Specifications						
Packaging	Tube					
Reel Size (mm)	-					
Tape Width (mm)	-					
Basic Ordering Unit (pcs)	450					
Packing Code	C11					
Marking	RGTV80TS65					
	Packaging Reel Size (mm) Tape Width (mm) Basic Ordering Unit (pcs) Packing Code					

● Absolute Maximum Ratings (at T_C = 25°C unless otherwise specified)

			1	
Parameter		Symbol	Value	Unit
Collector - Emitter Voltage		V _{CES}	650	V
Gate - Emitter Voltage		V _{GES}	±30	V
Collector Current	$T_C = 25^{\circ}C$	I _C	78	А
	T _C = 100°C	I _C	40	А
Pulsed Collector Current		I _{CP} ^{*1}	160	А
Power Dissipation	$T_C = 25^{\circ}C$	P _D	234	W
	$T_C = 100$ °C	P _D	117	W
Operating Junction Temperature		T _j	-40 to +175	°C
Storage Temperature		T _{stg}	-55 to +175	°C

^{*1} Pulse width limited by T_{imax.}

●Thermal Resistance

Parameter	Symbol	Values			Unit
raidilletei	Symbol	Min.	Тур.	Max.	Offic
Thermal Resistance IGBT Junction - Case	$R_{\theta(j-c)}$	-	-	0.64	°C/W

●IGBT Electrical Characteristics (at T_i = 25°C unless otherwise specified)

Parameter	Symbol	Conditions	Values			Linit
			Min.	Тур.	Max.	Unit
Collector - Emitter Breakdown Voltage	BV _{CES}	$I_{C} = 10 \mu A, V_{GE} = 0 V$	650	ı	1	V
Collector Cut - off Current	I _{CES}	$V_{CE} = 650V, V_{GE} = 0V$	-	ı	10	μΑ
Gate - Emitter Leakage Current	I _{GES}	$V_{GE} = \pm 30V$, $V_{CE} = 0V$	-	ı	±200	nA
Gate - Emitter Threshold Voltage	$V_{GE(th)}$	$V_{CE} = 5V, I_{C} = 27.5 \text{mA}$	5.0	6.0	7.0	V
Collector - Emitter Saturation Voltage	V _{CE(sat)}	$I_{C} = 40A, V_{GE} = 15V,$ $T_{j} = 25^{\circ}C$ $T_{j} = 175^{\circ}C$	-	1.5 1.85	1.9 -	V

●IGBT Electrical Characteristics (at T_j = 25°C unless otherwise specified)

Parameter	Symbol	Conditions		Unit		
			Min.	Тур.	Max.	Offic
Input Capacitance	C _{ies}	$V_{CE} = 30V,$ $V_{GE} = 0V,$	-	2370	-	pF
Output Capacitance	C _{oes}		-	94	-	
Reverse transfer Capacitance	C _{res}	f = 1MHz	-	38	-	
Total Gate Charge	Q_g	V _{CE} = 400V,	-	81	-	nC
Gate - Emitter Charge	Q_{ge}	$I_{\rm C} = 40A$,	-	17	-	
Gate - Collector Charge	Q_{gc}	V _{GE} = 15V	-	31	-	
Turn - on Delay Time	t _{d(on)}		-	39	-	
Rise Time	t _r	$I_C = 40A, V_{CC} = 400V,$ $V_{GF} = 15V, R_G = 10\Omega,$	-	17	-	20
Turn - off Delay Time	t _{d(off)}	$T_i = 25^{\circ}C$	-	113	-	ns ns
Fall Time	t _f	Inductive Load	-	45	-	
Turn - on Switching Loss	E _{on}	*E _{on} include diode reverse recovery	-	1.02	-	mJ
Turn - off Switching Loss	E _{off}	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	-	0.71	-	
Turn - on Delay Time	t _{d(on)}		-	38	-	
Rise Time	t _r	$I_C = 40A$, $V_{CC} = 400V$, $V_{GE} = 15V$, $R_G = 10\Omega$, $T_i = 175^{\circ}C$	-	19	-	ns
Turn - off Delay Time	$t_{d(off)}$		-	130	-	
Fall Time	t _f	Inductive Load	-	86	-	
Turn - on Switching Loss	E _{on}	*E _{on} include diode reverse recovery	-	1.07	-	m l
Turn - off Switching Loss	E _{off}		-	1.01	-	mJ
Reverse Bias Safe Operating Area	RBSOA	$I_C = 160A$, $V_{CC} = 520V$, $V_P = 650V$, $V_{GE} = 15V$, $R_G = 100\Omega$, $T_j = 175^{\circ}C$	FULL SQUARE		-	
Short Circuit Withstand Time	t _{sc}	$V_{CC} \le 360V$, $V_{GE} = 15V$, $T_j = 25^{\circ}C$	2	-	-	μs

• Electrical Characteristic Curves




Fig.2 Collector Current vs. Case Temperature 90 80 70 Collector Current : Ic [A] 60 50 40 30 20 T_j ≤ 175°C V_{GE} ≥ 15V 10 0 25 50 75 100 125 150 175 Case Temperature : T_C [°C]

Fig.3 Forward Bias Safe Operating Area





Fig.4 Reverse Bias Safe Operating Area



4/9

Electrical Characteristic Curves

Fig.5 Typical Output Characteristics




Fig.6 Typical Output Characteristics




Fig.7 Typical Transfer Characteristics





Fig.8 Typical Collector to Emitter Saturation Voltage vs. Junction Temperature



ROHM

Collector To Emitter Saturation

Voltage: V_{CE(sat)} [V]

Electrical Characteristic Curves

Fig.9 Typical Collector to Emitter Saturation Voltage vs. Gate to Emitter Voltage




Fig.10 Typical Collector to Emitter Saturation Voltage vs. Gate to Emitter Voltage




Fig.11 Typical Switching Time vs. Collector Current





Fig.12 Typical Switching Time vs. Gate Resistance



Collector To Emitter Saturation

Voltage: V_{CE(sat)} [V]

•Electrical Characteristic Curves

Fig.13 Typical Switching Energy Losses vs. Collector Current




Fig.14 Typocal Switching Energy Losses vs. Gate Resistance




Fig.15 Typical Capacitance vs. Collector to Emitter Voltage






Fig.16 Typical Gate Charge




• Electrical Characteristic Curves

Fig.17 Typical IGBT Transient Thermal Impedance



●Inductive Load Switching Circuit and Waveform






Fig.19 Inductive Load Waveform

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/