



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	CD with software User manual USB cable
Max runtime	4 min
Number of tare power	41 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS

### Physical

Cable length	1.48 m
Number of rack unit	2U
Colour	Black
Depth	31.2 cm
Height	8.6 cm
Net weight	11 kg
USB compatible	Yes
Width	43.7 cm

### Input

Network frequency	40...70 Hz
Plug standard	IEC 60320 C14
Input voltage limits	100...280 V adjustable (half load) 160...280 V
Inputvolt_other	220 V 240 V
Number of cables	1

Input voltage	230 V
---------------	-------

## Output

Rated power in W	800 W
Maximum configurable power in W	800 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Outputvolt_other	220 V 240 V
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Nb of power socket outlets	3 IEC 60320 C13
Bypass type	Internal bypass (automatic and manual)
Curve equation	Efficiency
Curve fixed loss	0.0468
Curve load maximum	100 %
Curve load minimum	5 %
Curve proportional loss	0.0447
Curve square loss	0.0209
Curve X-axis maximum	100 %
Curve test cond ID	Curve fit of data measured in accordance with the ENERGY STAR Test Method for Uninterruptible Power Supplies. All measurements taken in normal mode(s), at typical environmental conditions, with 230V/50Hz electrical input and balanced resistive load (PF = 1.0) output.
Curve X-axis minimum	0 %
Curve X-axis title	Load
Curve X-axis units	Percentage
Curve Y-axis maximum	100 %
Curve Y-axis minimum	50 %
Curve Y-axis title	Efficiency
Curve Y-axis units	Percentage
Graph display	2
Output voltage	230 V
Maximum configurable power in VA	1000 VA
Rated power in VA	1000 VA
Runtime at 200W	00:24:00
Runtime at 400W	00:11:00
Transfer time	4 ms typical

## Conformance

Product certifications	CE
Standards	IEC 62040-1-1 IEC 62040-1-2

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...15000 m
Acoustic level	50 dB
Show note OP temperature	No
IP degree of protection	IP20

## Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 h
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Liquid value	0
Battery curve	D
Battery charger power	38 W rated

## Communications & Management

Free slots	1
Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	13.7 kg
Package 1 Height	21.8 cm
Package 1 width	45.5 cm
Package 1 Length	55.1 cm
Unit Type of Package 2	P12
Number of Units in Package 2	16
Package 2 Weight	221.6 kg
Package 2 Height	102 cm
Package 2 width	80 cm
Package 2 Length	120 cm

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------