F Series

DC-HVDC Converter



10 Watts

- Output Voltages from 100V to 12kV
- Output Voltage Proportional to Input
- Low Turn-on Voltage 0.7VDC
- Input to Output Isolation
- Dual Output Option
- Arc & Short Circuit Protected
- No Minimum Load
- 3 Year Warranty



The F Series is a broad line of robust, field-proven DC to HV DC converters which deliver 10 Watts continuous output power. Outputs range from 100V to 12kV. The input and output are galvanically isolated so a unit can be used to deliver a positive or negative high voltage output. The output voltage is proportional to input voltage with a low 0.7V typical turn-on voltage.

The F Series employs a quasi-sinewave oscillator, a fully enclosed transformer, input and output filtering, and a 5-sided metal enclosure. As a result, these modules exhibit very low EMI/RFI, noise and ripple. A dual output option has a center-tap pin which, when grounded provides both positive and negative outputs from one compact module.

Dimensions:

F Series:

2.80 x 1.70 x 0.85" (71.1 x 43.2 x 21.6mm)

Key Applications:

- Mass Spectrometry
- Electrostatic Chucks
- Electrophoresis
- Capacitor ChargingParticle Counter
- Isolation Testing
- Medical Laser Treatment

Input					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage	0.7		12, 15	VDC	See Models and Ratings Table.
Input Current, No Load			500	mA	
Input Current, Full Load			1.5	А	

Output								
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions			
Output Voltage			12,000	VDC	See Models and Ratings Table			
Output Current			100	mA	See Models and Ratings Table			
Output Voltage Tolerance		+5, -5		%	At Max Vout, Full Load			
Minimum Load	No minimum load required							
Regulation	Unregulated, Output is proportional to Input. See Application Notes.							
Short Circuit Protection	Protected against short circuit conditions indefinitely.							
Ripple and Noise	0.1		2.5	%	See Models and Ratings Table.			
Response Time			260	msec	0 to Max Vout, Full Load			

Notes

- Maximum rated output current is available at maximum rated output voltage and derates linearly as input voltage is decreased.
- Output voltage is load dependent. Under light or no-load conditions, reduce the input voltage so maximum rated output voltage is not exceeded.
- 3. Specifications after 1 hour warm-up, full load, at 25°C unless otherwise indicated.
- 4. Proper thermal management techniques are required to maintain safe case temperature at maximum power output.
- Ripple specification for center-tapped units applies to the voltage between the positive and negative output terminals.




Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Operating Temperature (case)	-10		+70	°C	Standard operating temperature	
Storage Temperature	-25		+90	°C		
Humidity			95	%RH	Non-condensing	
Cooling					Natural Convection	


General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Isolation: Input to Output			3,500	V	< ±3,500 Bias for Models F01 to F60	
Isolation: Input to Output			500	V	< ±500 Bias for Models F70 to F121	
Switching Frequency	25		125	kHz	Stable frequency over entire output voltage range.	
Construction	Case materia	Case material is black anodized aluminum. UL 94 V-0 rated solid vacuum encapsulation.				
Mean Time Between Failure	810			kHrs	Bellcore TR 332	

Block Diagram



Case Temperature Hot Spot





Models & Ratings

Output Voltage	Output Current	Input Voltage	Ripple	Material	
0 to 100V	100mA	0 to 12V	<0.6%	F01	
0 to 200V	50mA	0 to 12V	<1.0%	F02	
0 +/-100V	50mA	0 to 12V	<1.0%	F02CT	
0 to 200V	50mA	0 to 12V	<1.0%	F02RH	
0 to 300V	33.3A	0 to 12V	<1.0%	F03	
0 to +/-150V	33.3A	0 to 12V	<1.0%	F03CT	
0 to 300V	33.3A	0 to 12V	<1.0%	F03H	
0 to 400V	25mA	0 to 12V	<1.0%	F04	
0 to +/-200V	25mA	0 to 12V	<1.0%	F04CT	
0 to +/-200V	25mA	0 to 12V	<1.0%	F04CTH	
0 to 400V	25mA	0 to 12V	<1.0%	F04H	
0 to 500V	20mA	0 to 12V	<0.1%	F05	
0 to 500V	20mA	0 to 12V	<0.1%	F05H	
0 to 600V	16mA	0 to 12V	<0.1%	F06	
0 to +/-300V	16mA	0 to 12V	<0.1%	F06CT	
0 to 800V	12.5mA	0 to 12V	<0.1%	F08	
0 to 1000V	10mA	0 to 12V	<0.1%	F10	
0 to +/-500V	10mA	0 to 12V	<0.1%	F10CT	
0 to 1200V	8.3mA	0 to 12V	<0.1%	F12	
0 to +/-600V	8.3mA	0 to 12V	<0.1%	F12CT	
0 to 1500V	6.6mA	0 to 12V	<0.1%	F15	
0 to +/-750V	6.6mA	0 to 12V	<0.1%	F15CTH	
0 to 1500V	6.6mA	0 to 12V	<0.1%	F15H	
0 to 2000V	5mA	0 to 12V	<1.0%	F20	
0 to 3000V	3.3mA	0 to 15V	<1.0%	F30	
0 to +/-1500V	3.3mA	0 to 15V	<1.0%	F30CT	
0 to 3000V	3.3mA	0 to 15V	<1.0%	F30H	
0 to 4000V	2.5mA	0 to 15V	<1.0%	F40	
0 to +/-2000V	2.5mA	0 to 15V	<1.0%	F40CT	
0 to 5000V	2mA	0 to 15V	<1.0%	F50	
0 to +/-2500V	2mA	0 to 15V	<1.0%	F50CT	
0 to 6000V	1.66mA	0 to 15V	<1.0%	F60	
0 to +/-3000V	1.66mA	0 to 15V	<1.0%	F60CT	
0 to 6000V	1.66mA	0 to 15V	<1.0%	F60H	
0 to 8000V	1.25mA	0 to 15V	<2.5%	F80	
0 to +/-4000V	1.25mA	0 to 15V	<2.5%	F80CT	
0 to 10,000V	1mA	0 to 15V	<2.5%	F101R	
0 to 12,000V	0.83mA	0 to 15V	<2.5%	F121	
0 to +/-6000V	0.83mA	0 to 15V	<2.5%	F121CT	


Notes -

- 1. All orderable part numbers are listed above.
- 2. CT indicates dual output, center tap.
- 3. H suffix indicates drilled mounting holes for F01 to F60.
- 4. R suffix is used as a RoHS indicator for legacy models.




Mechanical Details

F01 - F60



F80 - F121




Notes

- 1. All dimensions are in inches (mm)
- 2. Weight 5oz (142g)
- 3. Tolerance: X.XX±0.02 (0.51)
- 4. Pin Tolerance: ±0.005 (0.127)
- 5. Case is internally connected to (-) Input.




Application Notes


Positive Output



Negative Output



Dual Output



Output Voltage vs. Input Voltage

