

1.5 Watts

- Output Voltages from 100V to 6kV
- Output Voltage Proportional to Input
- Low Turn-on Voltage 0.7VDC
- Input to Output Isolation
- Dual Output Models
- No Minimum Load
- 3 Year Warranty



The G Series is a line of miniature high voltage converters that provide up to 6kV output, positive or negative, in a compact PCB mount package. The isolated output is directly proportional to the input, and is linear from approximately 0.7 volts in. Excellent filtering techniques and a low noise quasi-sinewave oscillator provide clean, reliable DC to HV DC conversion with low ripple and low EMI/RFI.

The isolated output allows for user selectable output polarity. When the optional center-tap pin is grounded, the unit provides both positive and negative outputs from one compact, low cost module. The pin pattern used on this model has become an industry standard for high voltage modules. The G Series units are component level converters that are easy to integrate, low cost, and come with decades of field proven reliability.

Dimensions:

G Series:

1.50 x 1.50 x 0.63" (38.1 x 38.1 x 16.0mm)

Key Applications:

- Mass Spectrometry
- Electrostatic Chucks
- Electrophoresis
- Capacitor Charging
- Particle Counter
- Ignition/Spark
- Sustaining Ion Pumps

Input					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage	0.7		12	VDC	
Input Current, No Load			175	mA	See Models and Ratings Table.
Input Current, Full Load			400	mA	See Models and Ratings Table.

Output						
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Output Voltage			6,000	VDC	See Models and Ratings Table	
Output Current			15	mA	See Models and Ratings Table	
Output Voltage Tolerance		+3, -3		%	At Max Vout, Full Load	
Minimum Load	No minimum load required					
Regulation	Unregulated, Output is proportional to Input. Unloaded output voltage is typically 10% higher than unloaded.					
Ripple and Noise	0.1		2.0	%	See Models and Ratings Table.	
Response Time		15		msec	0 to Max Vout, Full Load [G01 to G60]	

Notes

- Maximum rated output current is available at maximum rated output voltage and derates linearly as input voltage is decreased.
- Output voltage is load dependent. Under light or no-load conditions, reduce the input voltage so maximum rated output voltage is not exceeded.
- Specifications after 30 minute warm-up, full load, at 25°C unless otherwise indicated.
- Proper thermal management techniques are required to maintain safe case temperature at maximum power output.
- Ripple specification for center-tapped units applies to the voltage between the positive and negative output terminals.
- Models G40, G50 & G60 do not have internal bleeder resistors on the output. Provisions must be made externally to discharge the output capacitors.



Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature (case)	-10		+60	°C	
Storage Temperature	-25		+90	°C	
Humidity			95	%RH	Non-condensing
Cooling					Natural Convection


General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Isolation: Input to Output			3,500	V	< ±3500 Bias	
Switching Frequency	60		190	kHz	Stable frequency over entire output voltage range.	
Construction	Case material is Diallyl Phthalate (DAP). UL 94 V-0 rated solid vacuum encapsulation.				d vacuum encapsulation.	
Mean Time Between Failure	2.29			MHrs Bellcore TR 332		


Safety Approvals

Safety Agency	Safety Standard	Notes & Conditions
UL	IEC/UL/CSA/EN 62368	
CE	CE Directive, RoHs and LVD	Where applicable
RoHS	RoHS 2 and 3 Directive (2011/65/EU)	Where applicable

Block Diagram



External EMI/RFI Shield



An AB suffix is used to indicate an added external EMI/RFI Shield as shown above. These five-sided aluminum enclosures feature a durable, non-conductive black anodized finish. On models with outputs of 3kV or higher, special care must be taken to ensure adequate spacing and insulation between the metal can and the high voltage output. Single sided layout, encapsulation, or conformal coating may be required. Case grounding studs must be connected to ground. Case ground is not connected to (-) Input.



Models & Ratings


Output Voltage	Output Current	Input (Current	Ripple	Model Number
Output Voltage	Output Ourrent	No Load Full Load		Nippie	Woder Number
0 to 100V	15mA	<100mA	<250mA	<1.75%	G01
0 to +/-50V	15mA	<100mA	<250mA	<1.75%	G01CT
0 to 200V	7.5mA	<100mA	<250mA	<0.75%	G02
0 to +/-100V	7.5mA	<100mA	<250mA	<0.75%	G02CTAB
0 to 300V	5mA	<100mA	<250mA	<0.75%	G03
0 to +/-150V	5mA	<100mA	<250mA	<0.75%	G03CTAB
0 to 400V	3.75mA	<100mA	<250mA	<0.75%	G04
0 to +/-200V	3.75mA	<100mA	<250mA	<0.75%	G04CTR
0 to 500V	3mA	<100mA	<250mA	<0.1%	G05
0 to 600V	2.5mA	<100mA	<250mA	<0.1%	G06
0 to 1000V	1.5mA	<100mA	<250mA	<0.1%	G10
0 to 1200V	1.25mA	<150mA	<275mA	<0.1%	G12
0 to 1200V	1.25mA	<150mA	<275mA	<0.1%	G12AB
0 to +/-600V	1.25mA	<150mA	<275mA	<0.1%	G12CTR
0 to 1500V	1mA	<125mA	<275mA	<0.5%	G15
0 to 1500V	1mA	<125mA	<275mA	<0.5%	G15AB
0 to 2000V	0.75mA	<165mA	<275mA	<0.5%	G20
0 to 2500V	0.6mA	<125mA	<275mA	<1%	G25
0 to 2500V	0.6mA	<125mA	<275mA	<1%	G25AB
0 to +/-1250V	0.6mA	<125mA	<275mA	<1%	G25CT
0 to 3000V	0.5mA	<125mA	<300mA	<2%	G30
0 to 3000V	0.5mA	<125mA	<300mA	<2%	G30AB
0 to +/-1500V	0.5mA	<125mA	<300mA	<2%	G30CT
0 to 4000V	0.37mA	<125mA	<300mA	<1%	G40
0 to 4000V	0.37mA	<125mA	<300mA	<1%	G40RAB
0 to 5000V	0.3mA	<125mA	<300mA	<2%	G50
0 to 5000V	0.3mA	<125mA	<300mA	<2%	G50AB
0 to +/-2500V	0.3mA	<125mA	<300mA	<2%	G50CT
0 to 6000V	0.25mA	<125mA	<300mA	<2%	G60
0 to 6000V	0.25mA	<125mA	<300mA	<2%	G60RAB
0 to +/-3000V	0.25mA	<125mA	<300mA	<2%	G60CT
0 to +/-3000V	0.25mA	<125mA	<300mA	<2%	G60CTAB
0 to 1250V	0.35mA	<35mA	<75mA	<0.05%	GPMT

Notes


- 1. All orderable part numbers are listed above.
- 2. CT indicates dual output, center tap. Negative side will be ~10% larger than positive side w.r.t. the center tap pin.
- 3. AB suffix indicates external shield, see Mechanicals.4. R suffix is used as a RoHS indicator for legacy models.
- 5. Model GPMT is rated for 0.4375 Watts.



Mechanical Details



G50 to G60 G25CT to G60CT



Pin #	Function		
1	(+) Input		
2	(-) Input		
3	(+) Output		
4	(-) Output		
5	Dual Output/Center Tap (Optional)		


Notes

- 1. All dimensions are in inches (mm)
- 2. Weight 1.5oz (43g)
- 3. Tolerance: X.XX±0.02 (0.51)
- 4. Pin Tolerance: ±0.005 (0.127)




Application Notes


Positive Output



Negative Output



Dual Output



Output Voltage vs. Input Voltage

