

Power PCB Relay RT1

- 1 pole 12A/16A, 1 form C (CO) or 1 form A (NO) contact
- **■** DC or AC coil
- 5kV/10mm coil-contact, reinforced insulation
- Ambient temperature 85°C (DC coil)
- WG version: product in accordance to IEC 60335-1
- Reflow version: for THR (Through-Hole Reflow) soldering process

Typical applications

Boiler control, timers, garage door control, POS automation, interface modules





VDE Cert. No. 40007571, cULus E214025, cCSAus 1142018; CQC 18002197247

Technical data of approved types on request

Contact Dat	а		12A		16A
Contact arrange	ement	1	form C (C	CO) or 1 forn	n A (NO)
Rated voltage				250VAC	
Max. switching	voltage			400VAC	
Rated current			12A 16A		16A
Limiting continu	ous current		12A	16A,	UL: 20A
Limiting making	current				
max. 4s, duty	y factor 10%		25A		30A
Breaking capac	ity max.		3000VA	40	000VA
Contact material				AgNi 90/10	gold plated
Frequency of op	peration, with/	without load			
DC coil				0/72000h ⁻¹	
AC coil			36	0/36000h ⁻¹	
Operate/release				8/6ms	
Bounce time ma				4/6ms	
Electrical endur	ance	se	e electric	al endurance	e graph ¹⁾
Contact rating	ıs				
Туре	Contact	Load			Cycles
IEC 61810					
RT314 DC-coil	A (NO)	16A, 250V	, ,	,	30x10 ³
RT314 DC-coil	C (CO)	16A, 250V	'AC, cosq	p=1, 85°C	10x10 ³
RT314 DC-coil	A (NO)	10A, 400V	AC, cosq	p=1, 85°C	150x10 ³

RT314 DC-coil	A (NO)	16A, 250VAC, cosφ=1, 85°C	30x10 ³
RT314 DC-coil	C (CO)	16A, 250VAC, cosφ=1, 85°C	$10x10^3$
RT314 DC-coil	A (NO)	10A, 400VAC, cosφ=1, 85°C	150x10 ³
RT114 DC-coil	A (NO)	12A, 250VAC, cosφ=1, 85°C	$50x10^3$
RT114 AC-coil	A (NO)	12A, 250VAC, cosφ=1, 70°C	100x10 ³
UL 508			
RT314	A/B (NO/NC)	20A, 250VAC, general purpose, 85°C	$C 6x10^3$
RT334	A (NO)	16A, 250VAC, gen. purpose, 85°C	$50x10^3$
RT314	A (NO)	1hp, 240VAC, 40°C	1x10 ³
RT314	A (NO)	FLA/LRA, 4.5/13.1A, 480VAC, 70°C	100x10 ³
EN60947-4-1			
RT314	A (NO)	250V/2A, AC-3	6.050







E0144-C









FN60947-5-1

reflow soldering process.

-11000-11 O I			
RT314 DC-coil	A/B (NO/NC)	2A, 24VDC, DC13	6.050
RT314	A (NO)	250/3A, AC-15	6.050
ENG0700 4			

RT314 DC-coil A (NO) 12(2)A, 250VAC, 85°C $100x10^{3}$ 1) For reflow solderable versions: actual contact performance may be influenced by the

Contact Data (continued)	
Mechanical endurance	
DC coil	>30x10 ⁶ operations
AC coil	>10x10 ⁶ operations
AC coil, reflow version	>5x10 ⁶ operations

Coil Data	
Coil voltage range, DC coil/ AC coil	5 to 110VDC / 24 to 230VAC
Operative range, IEC 61810	2
Coil insulation system according UL	class F

Coil versions, DC coil

Cail	Datad	Onoroto	Dalagas	Cail	Dotod soil
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	$\Omega \pm 10\%^{2)}$	mW
005	5	3.5	0.5	62	403
006	6	4.2	0.6	90	400
009	9	6.3	0.9	200	400
012	12	8.4	1.2	360	400
018	18	12.6	1.8	770	420
020	20	14.0	2.0	952	420
024	24	16.8	2.4	1440	400
048	48	33.6	4.8	5520	417
060	60	42.0	6.0	8570 ²⁾	420
110	110	77.0	11.0	288002)	420

2) Coil resistance ±12%.

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.


Coil versions, AC coil 50/60 Hz


Coil	Rated	Operate	Release	Coil	Rated coil			
code	voltage	voltage	voltage	resistance	power			
	VAC	VAC	VAC	$\Omega \pm 15\%^{(3)}$	VA			
524	24	18.0	3.6	350 ³⁾	0.76			
548	48	36.0	7.2	1420	0.74			
615	115	86.3	17.3	8100	0.76			
620	120	90.0	18.0	8800	0.75			
700	200	150.0	30.0	24350	0.76			
730	230	172.5	34.5	32500	0.74			
2) Coil registance +100/								

All figures are given for coil without pre-energization, at ambient temperature +23°C, 50 Hz.



Power PCB Relay RT1 (Continued)





Other coil voltages on request.

1000V _{rms}		
5000V _{rms}		
Clearance/creepage		
≥10/10mm		
Illa		
PTI 250V		
PTI 175V		
	5000V _{rms} ≥10/10mm Illa PTI 250V	

Other Data

Material compliance: EU RoHS/ELV. China RoHS. REACH. Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Resistance to heat and fire

according EN60335, par30 WG version or Reflow version

Ambient temperature

DC coil -40 to 85°C AC coil -40 to 70°C

Category of environmental protection, IEC 61810

standard version RTII - flux proof, RTIII - wash tight reflow version RTII - flux proof

S0418-CR

S0163-BG

Vibration resistance (functional)

form A/form B contact, 30 to 500Hz 20g/5g Shock resistance (destructive) 100g

Other Data (continued)

Terminal type standard version PCB-THT, plug-in PCB-THR reflow version

Mounting distance AC coil: ≥2.5mm Weight

Resistance to soldering heat THT, IEC 60068-2-20

270°C/10s RTIII 260°C/5s

Resistance to soldering heat THR

reflow soldering (for reflow version) forced gas convection 4) or vapour phase 5)

according EN61730 temperature profile Packaging/unit tube/20 pcs., box/500 pcs.


4) infrared heating not allowed 5) recommended fluid LS/230

Accessories

For details see datasheet Accessories Industrial Power Relay RT NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.


PCB layout / terminal assignment

Bottom view on solder pins




22,65±0,2







*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.





22,65±0,2


S0418-CA



















S0163-BC




Power PCB Relay RT1 (Continued)


Dimensions





Process conditions for Reflow soldering according to EN61760-1





Product code structure Typical product code RT 3 4 024 Type RT Power PCB Relay RT1 Version 12A, pinning 3.5mm, flux proof 12A, pinning 5mm, flux proof 2 16A, pinning 5mm, flux proof 12A, pinning 3.5mm, wash tight 12A, pinning 5mm, wash tight 16A, pinning 5mm, wash tight D **Contact arrangement** 1 1 form C (CO) contact 3 1 form A (NO) contact **Contact material** 4 AgNi 90/10 AgNi 90/10 gold plated (for type RT31.) Coil Coil code: please refer to coil versions table Version **Blank** Standard version Product in accordance with IEC 60335-1 (domestic appliances) WG

R

Reflow solderable



Power PCB Relay RT1 (Continued)

Product code	Version	Contacts	Contact material	Coil	Version	Part number
RT114009	12A,	1 form C (CO)	AgNi 90/10	9VDC	Standard	1393239-9
RT114012	pinning 3.5mm,	1 form C (CO)	1	12VDC		1419108-1
RT114012WG	flux proof	1 form C (CO)		12VDC	IEC60335-1 compliant	7-1415538-6
RT114024		1 form C (CO)		24VDC	Standard	1-1393239-3
RT114024WG		1 form C (CO)		24VDC	IEC60335-1 compliant	1415539-4
RT114730		1 form C (CO)		230VAC	Standard	1-1393239-9
RT115024		1 form C (CO)	AgNi 90/10 gold pl.	24VDC		2-1393239-1
RT134012		1 form A (NO)	AaNi 90/10	12VDC		2-1393239-6
RT134024		1 form A (NO)		24VDC		3-1393239-0
RT214012	12A.	1 form C (CO)		12VDC		5-1393239-4
RT214024	pinning 5mm,	1 form C (CO)		24VDC		5-1393239-5
RT214524	flux proof	1 form C (CO)		24VAC		5-1393239-9
RT214730	nax proof	1 form C (CO)		230VAC		1419108-6
RT314005	16A.	1 form C (CO)		5VDC		9-1393239-1
RT314006	pinning 5mm,	1 form C (CO)		6VDC		9-1393239-3
RT314009	flux proof	1 form C (CO)		9VDC		9-1393239-4
RT314012	liax proof	1 form C (CO)		12VDC		9-1393239-5
RT314012R		1 form C (CO)		12VDC	Reflow solderable	4-1415543-6
RT314012WG		1 form C (CO)		12VDC	IEC60335-1 compliant	8-1415535-6
RT314018		1 form C (CO)		18VDC	Standard	9-1393239-7
RT314018		1 form C (CO)		24VDC	Stariuaru	9-1393239-8
RT314024		1 form C (CO)		24VDC	IEC60335-1 compliant	1415538-7
RT314024VVG		1 form C (CO)		48VDC	Standard	1393240-1
RT314060		1 form C (CO)		60VDC	Staridard	1-1649328-7
RT314110		1 form C (CO)		110VDC		1393240-3
RT314524		1 form C (CO)		24VAC		1393240-4
RT314548		1 form C (CO)		48VAC	-	1393240-5
RT314615		1 form C (CO)		115VAC		1393240-6
RT314730		1 form C (CO)		230VAC		1393240-7
RT314730WG		1 form C (CO)		230VAC	IEC60335-1 compliant	4-1415538-0
RT315024		1 form C (CO)	AgNi 90/10 gold pl.	24VDC	Standard	1-1393240-4
RT334009WG		1 form A (NO)	AgNi 90/10	9VDC	IEC60335-1 compliant	3-1415538-1
RT334012		1 form A (NO)		12VDC	Standard	4-1393240-5
RT334012WG		1 form A (NO)		12VDC	IEC60335-1 compliant	1-1415527-1
RT334024		1 form A (NO)		24VDC	Standard	4-1393240-8
RT334048		1 form A (NO)		48VDC	- Staridard	5-1393240-0
RTB14005	12A.	1 form C (CO)		5VDC	-	1-1393238-2
RTB14003	pinning 3.5mm,	1 form C (CO)		12VDC	-	1-1393238-5
RTB14012	wash tight	1 form C (CO)		24VDC	-	1-1393238-9
RTB14024 RTB14524	wasirtigiit	1 form C (CO)		24VDC 24VAC	-	2-1393238-4
					-	
RTB34012	10A Eropo wook tiret	1 form A (NO)		12VDC	-	3-1393238-0
RTC14024	12A, 5mm, wash tight	1 form C (CO)		24VDC	-	5-1393238-0
RTD14005	16A,	1 form C (CO)	_	5VDC		5-1393238-9
RTD14012	pinning 5mm,	1 form C (CO)		12VDC	-	6-1393238-2
RTD14024	wash tight	1 form C (CO)	_	24VDC		6-1393238-8
RTD14048		1 form C (CO)		48VDC		6-1393238-9

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request