



Alcoswitch

TE Internal #: 1825535-1

Rotary Switches, 12 Position, Long Thin Knob Actuator Style, Rotary Switch Style, Rotary Rotary Switch Type, 12 Switch, Epoxy

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Rotary Switches



Number of Rotary Switch Positions: 12

Actuator Style: **Long Thin Knob**

Switch Style: **Rotary**

Rotary Switch Type: **Rotary**

Number of Switches: 12

Features

Product Type Features

Removable Tape Seal	Without
Product Type	Switch
Illuminated	No
Actuator Style	Long Thin Knob
Switch Style	Rotary
Rotary Switch Type	Rotary
Sealed Rotary Switch	No
Code Type	Single Pole
Angle of Throw	30

Configuration Features

Number of Rotary Switch Positions	12
Number of Switches	12

Electrical Characteristics

Rotary Switch Voltage Rating	20 VAC
------------------------------	--------

Contact Features

Solder Tail Contact Plating	Gold over Nickel
Rotary Switch Contact Current Rating	.4 A
Rotary Switch Contact Mating Area Plating Material	Gold
Contact Base Material	Brass



Mechanical Attachment

Rotary Switch Mounting Type	Printed Circuit Board
Rotary Switch Mounting Angle	Straight

Housing Features

Rotary Switch Housing Material	Epoxy
--------------------------------	-------

Usage Conditions

Oil-Tight	No
-----------	----

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Other

Comment	Adjustable
---------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (1.3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1825537-2
MRJE2604

TE Part # 1825537-3
MRJE3404

TE Part # 1825537-1
MRJE11204

TE Part # 1825535-3
MRJ3404

Customers Also Bought

TE Part #211772-1
CPC PLUG ASSEMBLY SIZE 23-19

TE Part #1-213928-1
CPC PSTD RCPT ASSY SZ 20-14 LF

TE Part #2-2176091-4
RP 2A 0.25W 100R 0.1% 25PPM 1K RL

TE Part #1614959-8
CPF0805 1M1 0.1% 25PPM 1K RL

TE Part #87456-1
06 MODIV HSG COMP DR .100CL

TE Part #171822-6
EIS REC. HSG 6P-NATURAL

TE Part #2-1393143-0
27E168=SOCKET,KU93,11,PC,NYL

TE Part #1-2213818-5
6X6 ILL TACT THT 100GF HI RED

TE Part #2-1393144-2
K10L-11A55-120=K10/K20

Documents

Product Drawings

MRJ11204

English

MRJ11204

Rotary Switches, 12 Position, Long Thin Knob Actuator Style, Rotary Switch Style,
Rotary Rotary Switch Type, 12 Switch, Epoxy

