



EMI Filters > IEC Unfiltered Inlets > CORCOM C SERIES IEC UNFILTERED INLETS



Filter Current Rating: 10 A

Input Connector Type: IEC 60320/C-14

Input Connector Style: Male Receptacle

Filter Output Termination Type: 3/16" Faston

Voltage Rating (Max): 250 VAC

[All CORCOM C SERIES IEC UNFILTERED INLETS \(8\)](#)

Features

Product Type Features

Input Connector Type	IEC 60320/C-14
Input Connector Style	Male Receptacle
Filter Output Termination Type	3/16" Faston

Electrical Characteristics

Filter Current Rating	10 A
Voltage Rating (Max)	250 VAC

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-102
CORCOM C SERIES MULTI-FUNCTION INLET FIL



TE Part # 1-1609112-4
15CBE1=F8274



TE Part # 1609142-1
GA400 POWER LINE CO=F6946

Also in the Series | Corcom C



IEC Unfiltered Inlets(8)



Multi-Function Inlet Filters(8)

Customers Also Bought



TE Part #1-6609113-3
10CFE1 S0=F7834




TE Part #1-2308341-3
FULL METAL HOODS SIZE 2-3 (RAW 180 DEG)



TE Part #1-2308342-5
FULL METAL HOODS SIZE 3-5 (RAW)



TE Part #T2010162201-000
HA-016-F



Documents

Product Drawings

10CE1 M0=F7804

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1609112-3_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1609112-3_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1609112-3_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

1654001_Corcom_Product_Guide_C_Series

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English



Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

C Series Appliance Inlet CB Certificate

English

C Series Appliance Inlet CB Test Report

English