

1A, 400V - 600V Standard Surface Mount Rectifier

FEATURES

- AEC-Q101 qualified
- Ideal for automated placement
- Low forward voltage drop
- Glass passivated chip junction
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- DC to DC converter
- Automotive application
- Car lighting
- Snubber
- General purpose

MECHANICAL DATA

- Case: Micro SMA
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.006g (approximately)

KEY PARAMETERS			
PARAMETER	VALUE	UNIT	
I _F	1	Α	
V_{RRM}	400 - 600	V	
I _{FSM}	20	Α	
T _{J MAX}	175	°C	
Package	Micro SMA		
Configuration	Single die		









Micro SMA



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)					
PARAMETER	SYMBOL	S1GMH	S1JMH	UNIT	
Marking code on the device		A5	A7		
Repetitive peak reverse voltage	V_{RRM}	400	600	V	
Reverse voltage, total rms value	$V_{R(RMS)}$	280	420	V	
Forward current	l _F		1	А	
Surge peak forward current 8.3ms single half sine wave superimposed on rated load	I _{FSM}	20		А	
Junction temperature	T_J	-55 to +175		°C	
Storage temperature	T_{STG}	-55 to +175		°C	

1



Taiwan Semiconductor

THERMAL PERFORMANCE			
PARAMETER	SYMBOL	ТҮР	UNIT
Junction-to-lead thermal resistance	$R_{\Theta JL}$	30	°C/W
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	110	°C/W

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage ⁽¹⁾	I _F = 1A, T _J = 25°C	V _F	-	1.10	V
Reverse current @ rated V _R ⁽²⁾	T _J = 25°C	1	-	1	μΑ
	T _J = 125°C	- I _R	-	50	μA
Junction capacitance	1MHz, V _R = 4.0V	CJ	5	-	pF
Reverse recovery time	IF = 0.5A, IR = 1.0A Irr = 0.25A	t _{rr}	780	-	ns

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION			
ORDERING CODE ⁽¹⁾	PACKAGE	PACKING	
S1xMH	Micro SMA	12,000 / Tape & Reel	

Notes:

1. "x" defines voltage from 400V(S1GMH) to 600V(S1JMH)

2 Version: A2103



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve




Fig.3 Typical Reverse Characteristics





Fig.2 Typical Junction Capacitance

Fig.4 Typical Forward Characteristics







Fig.5 Maximum Non-Repetitive Forward Surge Current



3







CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.6 Reverse Recovery Time Characteristic and Test Circuit Diagram






4 Version: A2103




PACKAGE OUTLINE DIMENSIONS

Micro SMA



DIM.	Unit (mm)		Unit (inch)
Dilvi.	Min.	Max.	Min.	Max.
Α	2.30	2.70	0.091	0.106
В	2.10	2.30	0.083	0.091
С	0.63	0.73	0.025	0.029
D	0.10	0.20	0.004	0.008
E	1.15	1.35	0.045	0.053
F	0.65	0.85	0.026	0.034
G	0.75	0.95	0.030	0.037
Н	0.55	0.75	0.022	0.030
I	1.10	1.50	0.043	0.059

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
Α	1.10	0.043
В	2.00	0.079
С	0.80	0.031
D	1.00	0.039
E	0.50	0.020

MARKING DIAGRAM



P/N = Marking Code ΥW = Data Code

5 Version: A2103



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.