multicomp PRO

RoHS Compliant





Material and Specifications

Coupling	Bayonet
Shell Material	PC, Nylon66, fire resistance: V-0
Insert Material	PPS, Max. Temperature 260°C
Contact Material	Brass with gold plating
Termination	Solder and Crimp
Cable outer diameter range	6mm to 10mm
IP Rating	IP67
Mating Cycle	500
Temperature Range	-40°C to +85°C
Insulation Resistance (MΩ)	2000ΜΩ

Contact Specifications

Number of Contact	2	3	4	2B	3B	4B	5	7	9	10
Male Contact Face View	2 1 • • •	1 0 2 0 3	●1 ● 2 · 4 · 4 · 4 · 4 · 4 · 4 · 4 · 4 · 4 ·	1 0 2 0			2.01 0.5 0.00 0.00	2 • 7 • 6 • • • • 3 • • • 5		2 • 1 • 8 • • 9 • 7 • • 10 • 6 • • 5 • 6
Rated Current (A)	10	10	5	15	15	15	5	5	5	5
Contact Diameter (mm)	Ø1.5 × 2	Ø1.5 × 3	Ø1 × 4	Ø2 × 2	Ø2 × 3	Ø2 × 4	Ø1 × 5	Ø1 × 7	Ø1 × 9	Ø1 × 10
Rated Voltage (AC. V)	500	500	500	500	500	500	500	400	400	400
Test Voltage (AC. V) 1 min.	1500	1500	1500	1500	1500	1500	1500	1200	1200	1200
Contact Resistance (mΩ)	2.5	2.5	5	2.5	2.5	2.5	5	5	5	5
Wire Size for solder (mm²/AWG)	≤2/14	≤2.14	≤0.75/18	≤2/14	≤2/14	≤2.14	≤0.75/18	≤0.75/18	≤0.75/18	≤0.75/18

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



multicomp PRO


Diagram

Cable Mount Connector










In-line Cable Mount Connector










Rear Panel Mount Connector












Dust Cap



Each Side can be male of lemale contact

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Page <2> 12/08/21 V1.0



Specification Table

Cable Mount Connector				In-line Cab	ole Mount Co	nnector	Rear Panel Mount Connector			
Cable Mount Plug			Cable N	lount Recept	acle	Panel Mount Receptacle				
MPN	Termination	Contact Gender	No. of Contacts	MPN	Termination	Contact Gender	MPN	Termination	Contact Gender	
MP007613	Solder	Pin	2	MP007623	Solder	Socket	MP007643	Solder	Socket	
MP007614	Solder	Pin	3	MP007624	Solder	Socket	MP007644	Solder	Socket	
MP007615	Solder	Pin	4	MP007625	Solder	Socket	MP007645	Solder	Socket	
MP007616	Solder	Pin	5	MP007626	Solder	Socket	MP007646	Solder	Socket	
MP007617	Solder	Pin	2	MP007627	Solder	Socket	MP007647	Solder	Socket	
MP007618	Solder	Pin	3	MP007628	Solder	Socket	MP007648	Solder	Socket	
MP007619	Solder	Pin	4	MP007629	Solder	Socket	MP007649	Solder	Socket	
MP007620	Solder	Pin	7	MP007630	Solder	Socket	MP007650	Solder	Socket	
MP007621	Solder	Pin	9	MP007631	Solder	Socket	MP007651	Solder	Socket	
MP007622	Solder	Pin	10	MP007632	Solder	Socket	MP007652	Solder	Socket	
MP007663	Crimp	Pin	2	MP007666	Crimp	Socket	MP007672	Crimp	Socket	
MP007664	Crimp	Pin	3	MP007667	Crimp	Socket	MP007673	Crimp	Socket	
MP007665	Crimp	Pin	4	MP007668	Crimp	Socket	MP007674	Crimp	Socket	

Note: These connectors are not included dust caps

Circular Connector with Dust Cap

	In-line Cable M	ount Connector	Rear Panel Mount Connector				
	Cable Moun	t Receptacle	Panel Mount Receptacle				
MPN	Termination	Contact Gender	No. of Contacts	MPN	Termination	Contact Gender	
MP007633	Solder	Socket	2	MP007653	Solder	Socket	
MP007634	Solder	Socket	3	MP007654	Solder	Socket	
MP007635	Solder	Socket	4	MP007655	Solder	Socket	
MP007636	Solder	Socket	5	MP007656	Solder	Socket	
MP007637	Solder	Socket	2	MP007657	Solder	Socket	
MP007638	Solder	Socket	3	MP007658	Solder	Socket	
MP007639	Solder	Socket	4	MP007659	Solder	Socket	
MP007640	Solder	Socket	7	MP007660	Solder	Socket	
MP007641	Solder	Socket	9	MP007661	Solder	Socket	
MP007642	Solder	Socket	10	MP007662	Solder	Socket	
MP007669	Crimp	Socket	2	MP007675	Crimp	Socket	
MP007670	Crimp	Socket	3	MP007676	Crimp	Socket	
MP007671	Crimp	Socket	4	MP007677	Crimp	Socket	

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





Connector Contacts

Description	Part Number
Male Stamped Crimp Contact, 5A, 24-20AWG	MP007603
Female Stamped Crimp Contact, 5A, 24-20AWG	MP007604
Male Machined Crimp Contact, 10A, 26-22AWG	MP007605
Male Machined Crimp Contact, 10A, 20AWG	MP007606
Male Machined Crimp Contact, 10A, 18AWG	MP007607
Male Machined Crimp Contact, 10A, 16AWG	MP007608
Female Machined Crimp Contact, 10A, 26-22AWG	MP007609
Female Machined Crimp Contact, 10A, 20AWG	MP007610
Female Machined Crimp Contact, 10A, 18AWG	MP007611
Female Machined Crimp Contact, 10A, 16AWG	MP007612

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

