

# 600W, 12V - 60V Surface Mount Transient Voltage Suppressor

#### **FEATURES**


- AEC-Q101 qualified
- · Glass passivated chip junction
- Maximum V<sub>BR</sub> temperature coefficient: 0.094%/°C
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

### **APPLICATIONS**

- Switching mode power supply (SMPS)
- Motor for BLDC
- Lighting application
- Battery Management System
- Automotive

### **MECHANICAL DATA**

- Case: SOD-128
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Uni-directional
- Weight: 0.029g (approximately)











SOD-128



| ABSOLUTE MAXIMUM RATINGS (T <sub>A</sub> = 25°C unless otherwise noted)              |                  |             |      |  |  |  |
|--------------------------------------------------------------------------------------|------------------|-------------|------|--|--|--|
| PARAMETER                                                                            | SYMBOL           | VALUE       | UNIT |  |  |  |
| Non-repetitive peak impulse power dissipation with 10/1000µs waveform <sup>(1)</sup> | P <sub>PPM</sub> | 600         | W    |  |  |  |
| Steady state power dissipation at T <sub>L</sub> = 25°C <sup>(2)</sup>               | $P_{D}$          | 7.14        | W    |  |  |  |
| Forward Voltage @ I <sub>F</sub> = 25A for Uni-directional only <sup>(3)</sup>       | V <sub>F</sub>   | 3.5         | V    |  |  |  |
| Junction temperature                                                                 | TJ               | -55 to +175 | °C   |  |  |  |
| Storage temperature                                                                  | T <sub>STG</sub> | -55 to +175 | °C   |  |  |  |

1

#### Notes:

- 1. Non-repetitive current pulse per fig.3 and derated above T<sub>A</sub>=25°C per Fig.1
- 2. Units mounted on PCB (5mm x 5mm Cu pad test board)
- 3. Pulse test with PW = 0.3ms



| THERMAL PERFORMANCE                    |                  |     |      |  |  |  |
|----------------------------------------|------------------|-----|------|--|--|--|
| PARAMETER                              | SYMBOL           | TYP | UNIT |  |  |  |
| Junction-to-lead thermal resistance    | $R_{\Theta JL}$  | 21  | °C/W |  |  |  |
| Junction-to-ambient thermal resistance | R <sub>OJA</sub> | 62  | °C/W |  |  |  |
| Junction-to-case thermal resistance    | R <sub>eJC</sub> | 16  | °C/W |  |  |  |

Thermal Performance Note: Units mounted on PCB (5mm x 5mm Cu pad test board)

| ELECTRICAL SPECIFICATIONS (T <sub>A</sub> = 25°C unless otherwise noted) |                                                                            |      |                                           |                                                           |                                                                                      |                                                               |                                                                           |      |
|--------------------------------------------------------------------------|----------------------------------------------------------------------------|------|-------------------------------------------|-----------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------|---------------------------------------------------------------------------|------|
| Part number Marking code                                                 | Breakdown<br>voltage<br>V <sub>BR</sub> @I <sub>T</sub><br>(V)<br>(Note 1) |      | Test<br>current<br>I <sub>T</sub><br>(mA) | Working<br>stand-off<br>voltage<br>V <sub>WM</sub><br>(V) | Maximum<br>blocking<br>leakage<br>current<br>I <sub>R</sub> @V <sub>WM</sub><br>(µA) | Maximum<br>peak impulse<br>current<br>I <sub>PPM</sub><br>(A) | Maximum<br>clamping<br>voltage<br>V <sub>C</sub> @I <sub>PPM</sub><br>(V) |      |
|                                                                          |                                                                            | Min  | Max                                       |                                                           |                                                                                      | (Note 1)                                                      | tp =10/1000 μs                                                            |      |
| SMA6S12AH                                                                | 6S012                                                                      | 13.4 | 14.8                                      | 1                                                         | 12                                                                                   | 1                                                             | 30.8                                                                      | 19.5 |
| SMA6S15AH                                                                | 6S015                                                                      | 16.8 | 18.5                                      | 1                                                         | 15                                                                                   | 1                                                             | 24.6                                                                      | 24.4 |
| SMA6S18AH                                                                | 6S018                                                                      | 20.1 | 22.2                                      | 1                                                         | 18                                                                                   | 1                                                             | 20.5                                                                      | 29.2 |
| SMA6S20AH                                                                | 6S020                                                                      | 22.4 | 24.7                                      | 1                                                         | 20                                                                                   | 1                                                             | 18.5                                                                      | 32.5 |
| SMA6S21AH                                                                | 6S021                                                                      | 23.5 | 25.9                                      | 1                                                         | 21                                                                                   | 1                                                             | 17.6                                                                      | 34.1 |
| SMA6S22AH                                                                | 6S022                                                                      | 24.6 | 27.2                                      | 1                                                         | 22                                                                                   | 1                                                             | 16.8                                                                      | 35.7 |
| SMA6S24AH                                                                | 6S024                                                                      | 26.8 | 29.6                                      | 1                                                         | 24                                                                                   | 1                                                             | 15.4                                                                      | 39.0 |
| SMA6S25AH                                                                | 6S025                                                                      | 27.9 | 30.9                                      | 1                                                         | 25                                                                                   | 1                                                             | 14.8                                                                      | 40.6 |
| SMA6S26AH                                                                | 6S026                                                                      | 29.1 | 32.1                                      | 1                                                         | 26                                                                                   | 1                                                             | 14.2                                                                      | 42.2 |
| SMA6S30AH                                                                | 6S030                                                                      | 33.5 | 37.1                                      | 1                                                         | 30                                                                                   | 1                                                             | 12.3                                                                      | 48.7 |
| SMA6S33AH                                                                | 6S033                                                                      | 36.9 | 40.8                                      | 1                                                         | 33                                                                                   | 1                                                             | 11.2                                                                      | 53.6 |
| SMA6S36AH                                                                | 6S036                                                                      | 40.2 | 44.5                                      | 1                                                         | 36                                                                                   | 1                                                             | 10.3                                                                      | 58.4 |
| SMA6S39AH                                                                | 6S039                                                                      | 43.6 | 48.2                                      | 1                                                         | 39                                                                                   | 1                                                             | 9.5                                                                       | 63.3 |
| SMA6S40AH                                                                | 6S040                                                                      | 44.7 | 49.4                                      | 1                                                         | 40                                                                                   | 1                                                             | 9.2                                                                       | 64.9 |
| SMA6S43AH                                                                | 6S043                                                                      | 48.1 | 53.1                                      | 1                                                         | 43                                                                                   | 1                                                             | 8.6                                                                       | 69.8 |
| SMA6S47AH                                                                | 6S047                                                                      | 52.5 | 58.1                                      | 1                                                         | 47                                                                                   | 1                                                             | 7.9                                                                       | 76.3 |
| SMA6S51AH                                                                | 6S051                                                                      | 57.0 | 63.0                                      | 1                                                         | 51                                                                                   | 1                                                             | 7.2                                                                       | 82.8 |
| SMA6S56AH                                                                | 6S056                                                                      | 62.6 | 69.2                                      | 1                                                         | 56                                                                                   | 1                                                             | 6.6                                                                       | 90.9 |
| SMA6S60AH                                                                | 6S060                                                                      | 67.1 | 74.1                                      | 1                                                         | 60                                                                                   | 1                                                             | 6.2                                                                       | 97.4 |

### Note:

1. Pulse test with PW = 30ms



Taiwan Semiconductor

| ORDERING INFORMATION         |         |                      |  |  |
|------------------------------|---------|----------------------|--|--|
| ORDERING CODE <sup>(1)</sup> | PACKAGE | PACKING              |  |  |
| SMA6SxxAH                    | SOD-128 | 14,000 / Tape & Reel |  |  |

# Note:

(1) "xx" defines voltage from 12V (SMA6S12AH) to 60V (SMA6S60AH)



### **CHARACTERISTICS CURVES**

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$ 

Fig.1 Pulse Power or Current vs. Initial Junction Temperature




Fig.3 Clamping Power Pulse Waveform




Fig.2 Steady State Power Derating




Fig.4 Typical Junction Capacitance






Fig.5 Typical Transient Thermal Impedance






### **PACKAGE OUTLINE DIMENSIONS**

**SOD-128** 




| DIM.  | Unit | (mm) | Unit (inch) |       |  |
|-------|------|------|-------------|-------|--|
| DIWI. | Min. | Max. | Min.        | Max.  |  |
| Α     | 3.60 | 4.00 | 0.142       | 0.157 |  |
| В     | 2.30 | 2.70 | 0.091       | 0.106 |  |
| С     | 1.60 | 1.90 | 0.063       | 0.075 |  |
| D     | 0.90 | 1.10 | 0.035       | 0.043 |  |
| E     | 0.10 | 0.22 | 0.004       | 0.009 |  |
| F     | 0.00 | 0.10 | 0.000       | 0.004 |  |
| G     | 0.30 | 0.60 | 0.012       | 0.024 |  |
| Н     | 0.40 | 0.80 | 0.016       | 0.031 |  |
| Ī     | 4.40 | 5.00 | 0.173       | 0.197 |  |

### **SUGGESTED PAD LAYOUT**



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| Α      | 2.10      | 0.083       |
| В      | 1.40      | 0.055       |
| С      | 4.40      | 0.173       |
| D      | 3.00      | 0.118       |
| E      | 5.80      | 0.228       |

### **MARKING DIAGRAM**



P/N = Marking Code ΥW = Date Code F = Factory Code



Taiwan Semiconductor

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.