



Fluke 700HTH-1 Hydraulic Test Hose

MPN - FLUKE-700HTH-1



Key features

- Hose and fittings connect directly to the Fluke 700HTP-1 test pressure port
- Includes plugs and caps to eliminate fluid loss in hose, eliminates the need to re-prime the hose
- Self-sealing fittings with easy finger tight connections
- Low volumetric expansion and a negligible pressure drop at rated pressures

Product Overview

Product overview: Fluke 700HTH-1 Hydraulic Test Hose

The Fluke 700HTH-1 hydraulic test hose is a 10,000 psi, 690 bar working pressure test hose that features stainless steel and nylon construction for use in connecting a Fluke-700HTP-1 or other hydraulic test pump to a unit under test.

The Fluke 700HTH-1 allows connection to both a Fluke pressure module and a calibration unit under test from a Fluke 700HTP-1 hydraulic test pump simultaneously. 700HTH-1 is compatible with water and non-corrosive oil.

Specifications

Specifications: Fluke 700HTH-1 Hydraulic Test Hose

Mechanical and General Specifications	
Minimum bend radius	60 mm / 2.36 in.
Temperature	- 40°C to +120°C, (-40°F to +250°F)
Material	Nylon, stainless steel, zinc, plated steel, and nitrile
Dimensions	.84 m (33 in) long without adapter fittings
Weight	412.8 g (.910 oz)
Warranty	One year

Models

Models: Fluke 700HTH-1 Hydraulic Test Hose

Fluke 700HTH-1

Hydraulic Test Hose

- Hose with (2) 1/4" NPT female output connections
- (2) adapters that to convert ¼: NPT female to 1/4" NPT male (include sealing caps)
- 1/4 in NPT female to 1/4 in BSP male adapter
- Instruction sheet