### SQJA16EP

www.vishay.com

**Vishay Siliconix** 

# Automotive N-Channel 60 V (D-S) 175 °C MOSFET




Top View	Bottom View			
PRODUCT SUMMARY				
V <sub>DS</sub> (V)	60			
$R_{DS(on)}(\Omega)$ at $V_{GS} = 10 V$	0.0030			
$R_{DS(on)}(\Omega)$ at $V_{GS} = 4.5 V$	0.0047			
I <sub>D</sub> (A)	278			
Configuration	Single			
Package	PowerPAK SO-8L			

#### **FEATURES**

- TrenchFET<sup>®</sup> power MOSFET
- AEC-Q101 qualified
- 100 % R<sub>q</sub> and UIS tested
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>





ABSOLUTE MAXIMUM RATING	<b>GS</b> (T <sub>C</sub> = 25 °C, unless	otherwise notec	l)		
PARAMETER		SYMBOL	LIMIT	UNIT	
Drain-source voltage		V <sub>DS</sub>	60	V	
Gate-source voltage		V <sub>GS</sub>	± 20	V	
Continuous drain current	T <sub>C</sub> = 25 °C <sup>a</sup>	1	278		
	T <sub>C</sub> = 125 °C	Ι <sub>D</sub>	166		
Continuous source current (diode conduction) <sup>a</sup>		۱ <sub>S</sub>	454	А	
Pulsed drain current <sup>b</sup>		I <sub>DM</sub>	575		
Single pulse avalanche current	L = 0.1 mH	I <sub>AS</sub>	48		
Single pulse avalanche energy		E <sub>AS</sub>	115	mJ	
Maximum power dissipation	T <sub>C</sub> = 25 °C	Р	500	W	
	T <sub>C</sub> = 125 °C	PD	166	vv	
Operating junction and storage temperature range		T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C	
Soldering recommendations (peak temperature) d		-	260	U	

THERMAL RESISTANCE RATINGS					
PARAMETER		SYMBOL	LIMIT	UNIT	
Junction-to-ambient	PCB mount <sup>c</sup>	R <sub>thJA</sub>	42	°C/W	
Junction-to-case (drain)		R <sub>thJC</sub>	0.30	0/10	

#### Notes

- b. Pulse test; pulse width  $\leq 300~\mu s,~duty~cycle \leq 2~\%$
- c. When mounted on 1" square PCB (FR4 material)

d. See solder profile (<u>www.vishay.com/doc?73257</u>). The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection

a. Package limited

www.vishay.com

Vishay Siliconix

SQJA16EP

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT	
Static	•	•		•	•	•		
Drain-source breakdown voltage	V <sub>DS</sub>	$V_{GS} = 0, I_D = 250 \ \mu A$ 6		60	-	-	v	
Gate-source threshold voltage	V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$		1.5	2.0	2.5	v	
Gate-source leakage	I <sub>GSS</sub>	$V_{DS} = 0 V, V_{GS} = \pm 20 V$		-	-	± 100	nA	
Zero gate voltage drain current		$V_{GS} = 0 V$	V <sub>DS</sub> = 60 V	-	-	1		
	I <sub>DSS</sub>	$V_{GS} = 0 V$	V <sub>DS</sub> = 60 V, T <sub>J</sub> = 125 °C	-	-	50	μA	
		$V_{GS} = 0 V$	V <sub>DS</sub> = 60 V, T <sub>J</sub> = 175 °C	-	-	250		
On-state drain current <sup>a</sup>	I <sub>D(on)</sub>	$V_{GS} = 10 V$	$V_{DS} \ge 5 V$	30	-	-	А	
Drain-source on-state resistance <sup>a</sup>		$V_{GS} = 10 V$	I <sub>D</sub> = 15 A	-	0.0026	0.0030	Ω	
	P	$V_{GS} = 10 V$	I <sub>D</sub> = 15 A, T <sub>J</sub> = 125 °C	-	-	0.00516		
	R <sub>DS(on)</sub>	$V_{GS} = 10 \text{ V}$	I <sub>D</sub> = 15 A, T <sub>J</sub> = 175 °C	-	-	0.0065		
		$V_{GS} = 4.5 V$	I <sub>D</sub> = 15 A	-	0.0036	0.0047		
Forward transconductance b	9 <sub>fs</sub>	V <sub>DS</sub>	= 15 V, I <sub>D</sub> = 10 A	-	75	-	S	
Dynamic <sup>b</sup>		<u>.</u>						
Input capacitance	C <sub>iss</sub>		V <sub>DS</sub> = 25 V, f = 1 MHz	-	3915	5485	pF	
Output capacitance	C <sub>oss</sub>	$V_{GS} = 0 V$		-	1780	2500		
Reverse transfer capacitance	C <sub>rss</sub>			-	65	95		
Total gate charge <sup>c</sup>	Qg		V <sub>DS</sub> = 30 V, I <sub>D</sub> = 10 A	-	56	84	nC	
Gate-source charge <sup>c</sup>	Q <sub>gs</sub>	$V_{GS} = 10 V$		-	13	-		
Gate-drain charge <sup>c</sup>	Q <sub>gd</sub>				5	-	1	
Gate resistance	Rg	f = 1 MHz		0.6	1.3	2.0	Ω	
Turn-on delay time <sup>c</sup>	t <sub>d(on)</sub>				13	20	ns	
Rise time <sup>c</sup>	tr	$V_{DD} = 30 \text{ V}, \text{ R}_{\text{L}} = 3.0 \Omega$ $\text{I}_{\text{D}} \cong 10 \text{ A}, \text{ V}_{\text{GEN}} = 10 \text{ V}, \text{ R}_{\text{g}} = 1 \Omega$		-	4	6		
Turn-off delay time <sup>c</sup>	t <sub>d(off)</sub>			-	34	50		
Fall time <sup>c</sup>	t <sub>f</sub>			-	6	9		
Source-Drain Diode Ratings and Chara	acteristics <sup>b</sup>	•		•	•	•		
Pulsed current <sup>a</sup>	I <sub>SM</sub>			-	-	575	Α	
Forward voltage	V <sub>SD</sub>	I <sub>F</sub> = 15 A, V <sub>GS</sub> = 0 V		-	-	1.1	V	
Body diode reverse recovery time	t <sub>rr</sub>	I <sub>F</sub> = 8 A, di/dt = 100 A/μs		-	54	108	ns	
Body diode reverse recovery charge	Q <sub>rr</sub>			-	64	128	nC	
Reverse recovery fall time	t <sub>a</sub>			-	26	-	ns	
Reverse recovery rise time	t <sub>b</sub>			-	30	-		
Body diode peak reverse recovery current	I <sub>RM(REC)</sub>			-	2.0	-	А	

Notes

a. Pulse test; pulse width  $\leq$  300 µs, duty cycle  $\leq$  2 %

b. Guaranteed by design, not subject to production testing

c. Independent of operating temperature


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

2



**Vishay Siliconix** 

### **TYPICAL CHARACTERISTICS** ( $T_A = 25 \text{ °C}$ , unless otherwise noted)



S21-0232-Rev. A, 15-Mar-2021

3


Document Number: 76726

For technical questions, contact: <u>automostechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




**Vishay Siliconix** 


### **TYPICAL CHARACTERISTICS** ( $T_A = 25 \text{ °C}$ , unless otherwise noted)




**On-Resistance vs. Junction Temperature** 




Drain Source Breakdown vs. Junction Temperature




Source Drain Diode Forward Voltage



**On-Resistance vs. Gate-to Source Voltage** 





a.  $V_{GS}$  > minimum  $V_{GS}$  at which  $R_{DS(on)}$  is specified

S21-0232-Rev. A, 15-Mar-2021

4 For technical questions, contact: <u>automostechsupport@vis</u> Document Number: 76726


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




# SQJA16EP

Vishay Siliconix

#### **TYPICAL CHARACTERISTICS** ( $T_A = 25 \text{ °C}$ , unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?76726.



Vishay

### Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.