

Features

- Universal Input 100~240VAC 50/60Hz
- IEC/EN/ANSI/AAMI ES 60601-1 (ED 3.1)
- EMC: IEC60601-1-2:2014(ED 4.0)
- Safety Approvals: cULus / UKCA / CB / PSE / FCC / CE / TUV / RoHS / REACH
- Means of Protection: 2 X MOPP
- Touch Current: < 100μA
- Single Output to 250W
- Regulated Output with Low Ripple Noise
- Safety Agency Requirements and EMI/EMS Certified
- Meets DoE Level VI, Energy Star, ErP Stage 2
- No Load Power Consumption Less Than 0.21W
- IEC C14 Connector
- Dimensions: L 204 x W 94 x H 43.5 (mm)

16AWG

Yes

Weight: 1145g

General Specification

Cable Type

Medical Approved



The purpose of the document is to specify a Single-phase AC input, single output switching power supply. This specification is for: Desktop Power Supplies 250W Series. This product is suitable for use in medical applications. This Specification defines the input, output, performance characteristics, environment, noise and safety requirements.

Models			
Model Number	Output Voltage	Output Current	Output Power
44ATM250T-P120	12V DC	20A	240W
44ATM250T-P150	15V DC	16.66A	250W
44ATM250T-P240	24V DC	10.4A	250W

Туре	Switched Mode Power Supply	
Input Connector	IEC 320-C14	
Output Connection	6 Pin Molex 39-01-2060	
Number of Outputs	1	
Energy Efficiency Level	VI	
Mounting Style	Desktop	
MTBF	300,000 hours calculated at 25°C, by Telcoria SR-332	
Power Indicator	LED Indicator for power on	
Cable Length	1200mm(+30mm)	



44ATM250T-P 250W Desktop Series

Mechanical Specifications

Housing Material	Fully Enclosed Plastic Case
Overall Dimensions	204mm x 94mm x 43.5mm
Overall Length	204mm
Overall Height	43.5mm
Overall Width	94mm
Weight	1145g

Input Specifications

Rated Input Voltage	100~240Vac (±10%)
Rated Frequency	50/60Hz
Efficiency Level VI	Level VI / Efficiency (EU) 2019/1782
Input Current	3.3A-1.3A
Inrush Current	100A Max. / 230Vac (Cold Start At 25°C, Full Load)
Touch Current	Less than 100μA
Input Protection	Internal Primary Current Fuse

Output Specifications

Output Regulation	±5%
Ripple & Noise (max.)	1% Vp-p Max. for Output Voltage @ Full Load
Voltage Tolerance	±5%
Load Regulation	±5%
No Load Power Consumption	<0.21W
Number of Outputs	1
Insulation Class	
Dielectric Strength	Primary to Secondary 4,000Vac for 1 Minutes
Isolation Resistance	10M Ω for 500Vdc
Over Circuit Protection	Auto-recovery
Over Voltage Protection	V out * 150% MAX., latch off
Over Current Protection	l out * 150% MAX., auto-recovery

Protection Category

Means of Protection	2 X MOPP		



44ATM250T-P 250W Desktop Series

Approvals

Compliance/Certifications	CB / cULus/ FCC / CE / UKCA / T-mark / TUV / PSE
Safety Standard	IEC/EN/ANSI/AAMI ES 60601-1
EMC Emission:	Directive 93/42/EEC (EN 60601-1-2)

