
Data Sheet





Description

The Moonstone[™] 1W Power LED Light Source is a high performance energy efficient device which can handle high thermal and high driving current. The exposed pad design has excellent heat transfer from the package to the motherboard.

The low profile package design is suitable for a wide variety of applications especially where height is a constraint.

The package is compatible with reflow soldering. This will give more freedom and flexibility to the light source designer.

Applications

- Sign backlight, billboard illumination or backlight
- Exit sign or emergency sign lightings
- Commercial lightings
- Accent and marker lightings
- Pathway lighting
- Task lighting
- Reading lights
- Decorative lighting
- Garden lighting
- Architectural lighting
- Portable (flash light, bicycle head light

Features


- Available in Cool White & Warm White color
- Energy efficient
- Exposed pad for excellent heat transfer
- Suitable for reflow soldering process
- High current operation
- Long operation life
- Wide viewing angle
- Silicone encapsulation
- Non-ESD sensitive (threshold > 16KV)
- MSL 2a products
- Available in both electrically isolated and non-isolated metal heat slug


Specifications

- InGaN Technology
- 4.0 V (max) at 350 mA
- 110° viewing angle



Package Dimensions





Notes:

- 1. All dimensions are in millimeters.
- 2. Tolerance is ± 0.1 mm unless otherwise specified.

3. Metal slug is connected to anode for electrically non-isolated option.

Device Selection Guide (T_J = 25° C)


		Lu	minous Flux, 🤆	$\Phi_{v}^{[1,2]}$ (lm)			Electrically
Color	Part Number	Min.	Тур.	Max.	Test Current (mA)	Dice Technology	lsolated Metal Slug
Cool White	ASMT-MW03	43	55	73	350	InGaN	No
	ASMT-MW04						Yes
Warm White	ASMT-MY03	43	50	73	350	InGaN	No
	ASMT-MY04						Yes
Cool White Diffused	ASMT-MWB3	33	50	73	350	InGaN	No
	ASMT-MWB4						Yes
Warm White Diffused	ASMT-MYB3	33	45	73	350	InGaN	No
	ASMT-MYB4						Yes

Notes:

1. Φ_V is the total luminous flux output as measured with an integrating sphere at 25ms mono pulse condition.

2. Flux tolerance is $\pm 10\%$.

Part Numbering System



Absolute Maximum Ratings

Parameter	ASMT-Mxx3 / ASMT-Mxx4	Units
DC Forward Current ^[1]	350	mA
Peak Pulsing Current ^[2]	500	mA
Power Dissipation	1400	mW
Reverse Voltage	5	V
LED Junction Temperature	125	°C
LED Junction Temperature for short term application	145	°C
Operating Metal Slug Temperature Range at 350 mA	-40 to +110	°C
Storage Temperature Range	-40 to +120	°C
Soldering Temperature	Refer to Figure	8

Note:

Derate linearly based on Figure 6.
 Pulse condition: duty factor = 10%, Frequency = 1 kHz.

Optical Characteristics at 350 mA ($T_J = 25^{\circ}C$)

		Correlated Color Temperature, CCT (Kelvin)		Viewing Angle, $2\theta_{1/2}$ ^[2] (°)	Luminous Efficiency (Im/W)
Part Number Color	Color	Min.	Max.	Тур.	Тур.
ASMT-MW03	Cool White	4000	10000	110	45
ASMT-MW04					
ASMT-MY03	Warm White	2600	4000	110	41
ASMT-MY03					
ASMT-MWB3	Cool White Diffused	4000	10000	110	41
ASMT-MWB4					
ASMT-MYB3	Warm White Diffused	2600	4000	110	37
ASMT-MYB4					

Notes:

1. $\theta_{1\!\!/_2}$ is the off-axis angle where the luminous intensity is 1/2 the peak intensity.

Electrical Characteristic at 350 mA ($T_J = 25^{\circ}C$)

	Forward Voltage, V _F (Volts) at I _F = 350 mA		Thermal Resistance, Rθ _{j-ms} (°C/W) ^[1]	
Dice Type	Min.	Тур.	Max.	Тур.
InGaN	2.8	3.5	4.0	10

Note:

1. $R\theta_{j\text{-ms}}$ is the Thermal Resistance from LED junction to metal slug.




Figure 1. Relative Intensity vs. Wavelength.




Figure 2. Relative Luminous Flux vs. Mono Pulse Current.




Figure 3. Forward Current vs. Forward Voltage.




Figure 5. Relative Light Output vs. Junction Temperature.

1 0.9 0.8 **NORMALIZED INTENSITY** 0.7 0.6 0.5 0.4 0.3 0.2 0.1 0 -30 Ò 30 60 90 -90 -60 **ANGULAR DISPLACEMENT - DEGREES**

Figure 4. Radiation Pattern.




Figure 6. Maximum Forward Current vs. Ambient Temperature. Derated based on T_{JMAX} = 125°C, $R \theta_{J-A}$ = 30°C/W, 40°C/W and 50°C/W.




Figure 7. Maximum Forward Current vs. Metal Slug Temperature. Derated based on T_{JMAX} = 125°C, $R \Theta_{J-MS}$ = 10°C/W.






Figure 8. Recommended Reflow Soldering.





Option Selection Details

$\textbf{ASMT-Mxxx} - \textbf{N} \ \textbf{x}_1 \ \textbf{x}_2 \ \textbf{x}_3 \ \textbf{x}_4$

x₁ – Minimum Flux Bin

- x₂ Maximum Flux Bin x₃ – Color Bin Selection
- x₄ Packaging Option

Flux Bin Limit [x₁ x₂]

Luminous Flux	Luminous Flux (Im) at I _F = 350mA		
Min.	Max.		
33.0	43.0		
43.0	56.0		
56.0	73.0		
	Min. 33.0 43.0	Min. Max. 33.0 43.0 43.0 56.0	

Tolerance for each bin limits is $\pm 10\%$.

Color Bin Selections [x₃]

Individual reel will contain parts from one full bin only.

Cool White

cool white	
0	Full Distribution
A	A only
В	Bonly
С	C only
D	D only
E	E only
F	F only
G	G only
Н	H only
L	A and G only
Μ	B and H only
Ν	A and C only
Р	B and D only
Q	E and C only
R	F and D only
S	G and H only
U	E and F only
W	C and D only
Z	A and B only
1	A, B, C and D only
2	G, H, A and B only
4	C, D, E and F only

Full Distribution
A only
Bonly
C only
D only
E only
F only
A and C only
B and D only
E and C only
F and D only
E and F only
C and D only
A and B only
A, B, C and D only
C, D, E and F only

Color Bin Limit

Cool	Color	Limits			
White	(Chro	maticity Coo	rdinates)		
Bin A	Х	0.367	0.362	0.329	0.329
	Y	0.400	0.372	0.345	0.369
Bin B	Х	0.362	0.356	0.329	0.329
	Y	0.372	0.330	0.302	0.345
Bin C	Х	0.329	0.329	0.305	0.301
	Y	0.369	0.345	0.322	0.342
Bin D	Х	0.329	0.329	0.311	0.305
	Y	0.345	0.302	0.285	0.322
Bin E	Х	0.303	0.307	0.283	0.274
	Y	0.333	0.311	0.284	0.301
Bin F	Х	0.307	0.311	0.290	0.283
	Y	0.311	0.285	0.265	0.284
Bin G	Х	0.388	0.379	0.362	0.367
	Y	0.417	0.383	0.372	0.400
Bin H	Х	0.379	0.369	0.356	0.362
	Y	0.383	0.343	0.330	0.372

Warm White		Limits maticity Coo	rdinates)		
Bin A	Х	0.452	0.488	0.470	0.438
	Y	0.434	0.447	0.414	0.403
Bin B	Х	0.438	0.470	0.452	0.424
	Y	0.403	0.414	0.384	0.376
Bin C	Х	0.407	0.418	0.452	0.438
	Y	0.393	0.422	0.434	0.403
Bin D	Х	0.395	0.407	0.438	0.424
	Y	0.362	0.393	0.403	0.376
Bin E	Х	0.381	0.387	0.418	0.407
	Y	0.377	0.404	0.422	0.393
Bin F	Х	0.373	0.381	0.407	0.395
	Υ	0.349	0.377	0.393	0.362

Tolerance: ±0.01

Tolerance: ± 0.01




Figure 10. Color bins (Cool White).

Packaging Option [x₄]

Selection	Option
0	Tube
1	Tape and Reel




Figure 11. Color bins (Warm White).

Example

ASMT-MW03-NJKZ0

ASMT-MW03-Nxxx	x – Cool White, Electrically Non-isolated Heat Sink,
	Non-diffused
$X_1 = L$	– Minimum Flux Bin J
$X_2 = N$	– Maximum Flux Bin K
$X_3 = Z$	 Color Bin A and B only
$X_4 = 0$	 Tube Option

Packing Tube – Option 0





Figure 12. Tube dimensions.

Tape and Reel – Option 1



Dim	Value
Ao	8.80 ±0.10
Bo	16.45 ±0.10
Ko	3.60 ±0.10
E	1.75 ±0.10
F	11.50 ±0.10
W	24.0 ±0.10
Р	16.0 ±0.10
Quantity/ Reel	250 units

Figure 13. Carrier tape dimensions.

All dimensions in millimeters.




Figure 14. Carrier tape leader and trailer dimensions.




Figure 15. Reel dimensions.

Handling Precaution

The encapsulation material of the product is made of silicone for better reliability of the product. As silicone is a soft material, please do not press on the silicone or poke a sharp object onto the silicone. These might damage the product and cause premature failure. During assembly of handling, the unit should be held on the body only. Please refer to Avago Application Note AN 5288 for detail information.

Moisture Sensitivity

This product is qualified as Moisture Sensitive Level 2a per Jedec J-STD-020. Precautions when handling this moisture sensitive product is important to ensure the reliability of the product. Do refer to Avago Application Note AN5305 Handling of Moisture Sensitive Surface Mount Devices for details.

A. Storage before use

- Unopen moisture barrier bag (MBB) can be stored at <40°C/90%RH for 12 months. If the actual shelf life has exceeded 12 months and the humidity indicator card (HIC) indicates that baking is not required, then it is safe to reflow the LEDs per the original MSL rating.
- It is not recommended to open the MBB prior to assembly (e.g. for IQC).

- B. Control after opening the MBB
 - The humidity indicator card (HIC) shall be read immediately upon opening of MBB.
 - The LEDs must be kept at <30°C / 60%RH at all time and all high temperature related process including soldering, curing or rework need to be completed within 672 hours.
- C. Control for unfinished reel
 - For any unused LEDs, they need to be stored in sealed MBB with desiccant or desiccator at <5%RH.
- D. Control of assembly boards
 - If the PCB soldered with the LEDs is to be subjected to other high temperature processes, the PCB need to be stored in sealed MBB with desiccant or desiccator at <5%RH to ensure no LEDs have exceeded their floor life of 672 hours.
- E. Baking is required if
 - "60%" HIC indicator is NOT blue.
 - The LEDs are exposed to condition of $>30^\circ\text{C}$ / 60% RH at any time.
 - The LED floor life exceeded 672hrs.

Recommended baking condition: 60±5°C for 20hrs.

DISCLAIMER: Avago's products and software are not specifically designed, manufactured or authorized for sale as parts, components or assemblies for the planning, construction, maintenance or direct operation of a nuclear facility or for use in medical devices or applications. Customer is solely responsible, and waives all rights to make claims against Avago or its suppliers, for all loss, damage, expense or liability in connection with such use.

For product information and a complete list of distributors, please go to our web site: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries. Data subject to change. Copyright © 2005-2008 Avago Technologies. All rights reserved. AV02-1673EN - November 21, 2008

