

RoHS Compliant

Specifications

Dice material : AlGaInP/GaAs

Emmiting Colour : Green
Lens colour : Water clear
Peak wavelength : 573nm
Viewing angle : 130°
Luminous intensity (IV) : 90mcd

Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Rating	Unit
Power Dissipation	PD	72	mW
D.C Forward current	If	30	mA
Reverse Voltage	Vr	5	V
Operating Temperature	Тор	-30 to +80	°C
Storage Temperature	Tstg.	-40 to +85	°C
Peak Current(1/10Duty Cycle,0.1ms Pulse Width.)	If (peak)	80	mA
Soldering Temperature	Tsol	Reflow Soldering: 260°C for 10 sec.	

Electrical and Optical Characteristics

Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Luminous Intensity	lv	If=20mA	24.4	90		mcd
Forward Voltage	Vf	If=20mA		1.9	2.4	V
Peak Wavelength	λр	If=20mA		573		nm
Dominant Wavelength	λd	If=20mA		570		nm
Reverse Current	lr	Vr=5V			100	μA
Viewing Angle	201/2	If=20mA		130		deg
Spectrum Line Halfwidth	Δλ	If=20mA		20		nm

Notes


- 1. Tolerance of Luminous Intensity is ±15%
- 2. Tolerance of Forward Voltage is ±0.1V
- 3. Tolerance of Dominant Wavelength is ±1nm


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro







Typical Electrical/Optical Characteristic Curves (25°C Ambient Temperature Unless Otherwise Noted)


















Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





Dimensions



Tolerance is ±0.1mm unless otherwise noted.

Dimensions: Millimetres

Precautions in use:

Storage

Recommend storage environment:

Temperature: 5°C to 30°C (41°F to 86°F)

Humidity: 60% RH Max.

Use within 7 days after opening of sealed vapor/ESD barrier bags. Fold the opened bag firmly and keep in dry environment.

Soldering

Reflow Soldering

Recommend use of upper and lower heater type reflow furnace.

260°C Max for up to 5 seconds, one time only.

Pre-heat is 150°C Max for up to 2 minutes Max.

In case of screen-printing, keep metal mask thickness between 0.2mm and 0.3mm.

Cleaning


Surface condition of this device may change when organic solvents such as trichloroethylene or acetone were applied. Avoid using organic solvent.

Recommend ultrasonic method 300W Max.






Reflow Temp/Time



Reflow Soldering Pad Dimensions



Part Number Table

Description	Part Number
Chip LED, Green, 573nm, 130°, 90mcd, Surface Mount	MP008250

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

