3.00mm Round LED Lamp multicomp PRO

RoHS Compliant

Specifications

Dice material : GaP/GaP
Emmiting Colour : Green
Lens colour : Water Clear
Peak wavelength : 567nm
Viewing angle : 40°
Luminous intensity (IV) : 35mcd

Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Rating	Unit
Power Dissipation	PD	78	mW
D.C. Forward Current	lf	30	mA
Reverse Voltage	Vr	5	V
Reverse (Leakage) Current	lr	100	μΑ
Operating Temperature	Тор	-25 to +85	°C
Storage Temperature	Tstg.	-40 to +100	°C
Peak Current (1/10Duty Cycle, 0.1ms Pulse Width.)	If (peak)	100	mA
Soldering Temperature (1.6mm from body)	Tsol	Dip Soldering : 260°C for 5 sec. Hand Soldering : 350°C for 3 sec.	

Electrical and Optical Characteristics


Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Luminous Intensity	lv	If=20mA	20	35		mcd
Forward Voltage	Vf	If=20mA		2.1	2.6	V
Peak Wavelength	λр	If=20mA		567		nm
Dominant Wavelength	λd	If=20mA		572		nm
Reverse (Leakage) Current	lr	Vr=5V			100	μA
Viewing Angle	201/2	If=20mA		40		deg
Spectrum Line Halfwidth	Δλ	If=20mA		30		nm

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




3.00mm Round LED Lamp multicomp PRO


Typical Electrical/ Optical Characteristics Curves




FORWARD CURRENT VS.APPLIED VOLTAGE



FORWARD CURRENT VS. LUMINOUS INTENSITY



FORWARD CURRENT VS. AMBIENT TEMPERATURE




RADIATION DIAGRAM

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Page <2>

3.00mm Round LED Lamp multicomp PRO



Tolerance is ±0.25mm unless otherwise noted.

Dimensions: Millimetres

Part Number Table

Description	Part Number
Round LED, Green, 567nm, 40°, 35mcd, Through hole	MP008272

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

