# Rectangular LED Super Green, 2mm x 5mm



RoHS Compliant

#### **Specifications**

Dice Material : AllnGaP

Emitted colour : Super Green

Lens colour : Green Diffused

Peak wavelength : 570nm Viewing angle : 120° Luminous intensity (IV) : 60mcd

Electrical / Optical Characterisitics at Ta = 25°C								
Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition		
Luminous Intensity	IV	45	60	85	mcd			
Viewing Angle	201/2		120		deg			
Peak Emission Wavelength	λр		570		nm	IF = 20mA		
Dominant Wavelength	λD	568	571	575	nm	IF - ZUMA		
Spectral Line Half-Width	Δλ		18		nm			
Forward Voltage	VF	1.8	2	2.6	V			
Reverse Current	lr	-	-	10	uA	VR=5V		
▲ Luminous intensity (IV) ±10	%, Forward Vo	Itage (VF) ±0.1	V, Wavelength	(λd) ±0.5nm				


Absolute Maximum Ratings: (Ta = 25°C)							
Parameter	Symbol	Rating	Unit				
Power Dissipation	Pd	85	mW				
Peak Forward Current ( Duty 1/10 @ 1KHZ )	IF (Peak)	100	mA				
Recommended Operating Current	IF (Rec)	30	mA				
Electrostatic Discharge	ESDнвм	2000	V				
Operating Temperature Range	Topr	-40 to +85	°C				
Storage Temperature Range	Тѕтс	-40 to +100	°C				
Lead Soldering Temperature Range (1.6 mm (1/16 inch) from body)	Reflow Soldering: 260°C for 5 sec. Hand Soldering: 350°C for 3 sec.						

# Rectangular LED Super Green, 2mm x 5mm




## **Typical Electro-Optical Characteristics Curves**


### Super Green (AlInGaP \( \lambda P = 570nm \)




Forward Current vs. Forward Voltage



Forward current ( mA )  $Ta=25^{\circ}C$ Luminous Intensity vs. Forward current




Forward Current Derating Curve



Ambient Temperature Ta= °C Luminous Intensity vs. Ambient Temperature


# Rectangular LED Super Green, 2mm x 5mm





Relative Intensity VS. wavelength

#### **Dimensions**



Dimensions : Millimetres

#### Part Number Table

Description	Part Number
Rectangular LED, Super Green, 570nm, 120°, 60mcd, Through hole	MP007950

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Page <3> 16/08/21 V1.0