Round LED Light Bar Super Yellow, 22mm



RoHS Compliant

Specifications

Dice Material : AlInGaP
Emitted colour : Super Yellow
Epoxy colour : Yellow Diffused

Surface Ink colour : No Ink
Peak wavelength : 590nm
Luminous intensity (IV) : 25mcd

| Electrical / Optical Characterisitics at Ta = 25°C | | | | | | | | |
|--|--------|------|------|------|------|-------------|--|--|
| Parameter | Symbol | Min. | Тур. | Max. | Unit | Condition | | |
| Luminous Intensity | IV | 20 | 25 | 40 | mcd | | | |
| Viewing Angle | 201/2 | | | | deg | - IF = 20mA | | |
| Peak Emission Wavelength | λр | | 590 | | nm | | | |
| Dominant Wavelength | λD | 586 | 590 | 592 | nm | | | |
| Spectral Line Half-Width | Δλ | | 22 | | nm | | | |
| Forward Voltage | VF | 1.8 | 2 | 2.6 | V | | | |
| Reverse Current | lr | - | - | 10 | uA | VR=5V | | |
| ▲ Luminous intensity (IV) ±10%, Forward Voltage (VF) ±0.1V, Wavelength (λd) ±0.5nm | | | | | | | | |

| Absolute Maximum Ratings: (Ta = 25°C) | | | | | | | |
|---|---|-------------|------|--|--|--|--|
| Parameter | Symbol | Rating | Unit | | | | |
| Power Dissipation | Pd | 85 | mW | | | | |
| Peak Forward Current (Duty 1/10 @ 1KHZ) | IF (Peak) | 100 | mA | | | | |
| Recommended Operating Current | IF (Rec) | 30 | mA | | | | |
| Electrostatic Discharge | ESDнвм | 2000 | V | | | | |
| Operating Temperature Range | Topr | -40 to +85 | °C | | | | |
| Storage Temperature Range | Тѕтс | -40 to +100 | °C | | | | |
| Lead Soldering Temperature Range (1.6 mm (1/16 inch) from body) | Reflow Soldering: 260°C for 5 sec. Hand Soldering: 350°C for 3 sec. | | | | | | |

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Round LED Light Bar Super Yellow, 22mm




Typical Electro-Optical Characteristics Curves


Super Yellow (AllnGaP \(\lambda P = 590nm \)




Forward Current vs. Forward Voltage



Forward Current Derating Curve




Forward current (mA) $Ta{=}25^{\circ}\mathrm{C}$ Luminous Intensity vs. Forward current



 $\begin{array}{c} Ambient \ Temperature \ Ta=\ ^{\circ}C \\ Luminous \ Intensity \ vs. \ Ambient \ Temperature \end{array}$


Round LED Light Bar Super Yellow, 22mm





Relative Intensity VS. wavelength

Dimensions



Part Number Table

| Description | Part Number |
|---|-------------|
| Round LED Light Bar, Super Yellow, 22mm, 590nm, 25mcd | MP008001 |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

