



Pen-Style Control Cabinet Key with voltage tester

for all standard cabinets
and shut-off systems



NEW

- ▶ contactless detection of alternating current;
with optical indication
- ▶ range of voltage up to 600 V
(frequency range 50–60 Hz)
- ▶ do-it-yourself test by means of an optical
standby indicator for more certainty

KNIPEX Quality – Made in Germany

NEW


Pen-Style Control Cabinet Key with voltage tester

New additional feature allows reliable detection of alternating current in insulated cables, conductors, plugs and power sockets; also without current flow. After switching-on an LED indicates the readiness for operation; this provides certainty in application.






- ▶ with voltage tester for contactless detection of alternating current 50–60 Hz
- ▶ easy to carry pen-style control cabinet key with fastening clip
- ▶ four different key profiles can be utilized by swivelling the key holder
- ▶ for control cabinets and shut-off systems in the supply of gas, water and electricity
- ▶ for technical installations in buildings, e. g. air conditioning and ventilation systems, shut-off valves, mains switch-boards, etc.
- ▶ magnetic 1/4" bit adapter for standard bits as well as additional bit adapter for 1/4" bits inside one key profile
- ▶ cross recess PH 2 bit included
- ▶ battery compartment with bayonet catch for easy battery exchange (2 x LR44)
- ▶ corpus and fastening clip made from plastic material; tool holder and key profiles of diecast zinc




With double-bit key to open standard control cabinets



With contactless voltage tester for reliable detection of alternating current

Article-No.	EAN 4003773-	 mm	 mm	 mm	 mm	 g
00 11 17	068396	6/8	9	Ø 5 (internal) Ø 9 (external)	155	150



Your distributor



KNIPEX-Werk
C. Gustav Putsch KG

Oberkamper Strasse 13
42349 Wuppertal (Germany)

Tel.: +49 (0) 202 – 47 94-0
Fax: +49 (0) 202 – 47 74 94

info@knipex.de
www.knipex.de