

Han K 8/0 Pos. Insert 100 Amp. 10-25mm



Part number (09 38 008 2753
Specification	Han K 8/0 Pos. Insert 100 Amp. 10-25mm
HARTING eCatalogue h	https://b2b.harting.com/09380082753

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Series	Han-Com [®]
Identification	Han [®] K 8/0

Version

Termination method	Axial screw termination
Gender	Female
Size	24 B
Number of contacts	8
PE contact	Yes

Technical characteristics

Conductor cross-section	10 25 mm²
Wire outer diameter	≤11.4 mm
Rated current	100 A
Rated voltage	690 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated current acc. to UL	82 A
Rated voltage acc. to UL	600 V
Rated current acc. to CSA	100 A
Rated voltage acc. to CSA	600 V
Insulation resistance	>10 ¹⁰ Ω



Technical characteristics

Contact resistance	≤0.5 mΩ
Stripping length	13 14 mm
Tightening torque	6 Nm @ 10 mm² 6 Nm @ 16 mm² 7 Nm @ 25 mm²
Limiting temperature	-40 +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	323 g
Country of origin	Germany

Product data sheet 09 38 008 2753 Han K 8/0 Pos. Insert 100 Amp. 10-25mm



Commercial data

European customs tariff number 85366990

eCl@ss 27440205 Contact insert for industrial connectors