Emergency Stop Switch



Specifications

RoHS Compliant

Mechanical Life : >0.25 million operations
Electrical Life : >0.1 million operations

Electrical Durability : 1,000,000 cycles AC-15, 230V/1.6A 1,000,000 cycles DC-13, 24V/0.6A

Rated Insulation Voltage : 300V Rated Thermal Current : 5A

Contact Resistance : $100m\Omega$ max. (at 1A 6-8V DC) Insulation Resistance : $100M\Omega$ (at 500V DC)

Dielectric Strength : 2000V AC 50/60 Hz for 1 min

Panel Thickness : 0.8mm to 12mm

Degree of protection : IP66, Type 4X Indoor use only & Type 13

IP30 (under panel)

Storage Temperature : -40°C to +85°C

Operating Temperature : -25°C to +55°C

Operating Humidity : 45% to 85% RH

Wire Diameter : 16~26 AWG, 0.2~1.5mm²

Stripping Length : 8mm Torque : 1N*m

Contact Ratings (B300/R300)

Rated Insulation Voltage		300V			
Rated Thermal Current		5A			
Operating Voltage		12V	30V	125V	250V
AC	Resistive Load (AC-12)	5A	5A	4A	2A
50/60 Hz	Inductive Load (AC-15)	5A	5A	3A	1.5A
DC	Resistive Load (DC-12)	1A	1A	0.32A	0.16A
	Inductive Load (DC-13)	1A	1A	0.22A	0.11A

Contact Block Mounting Position

Contact			Operator Position		
Configuration	Mounting	Position	Free	Push	
10	1	NO		•	
	2	-			
20	1	NO		•	
	2	NO		•	
01	1	NC	•		
	2	-			
02	1	NC	•		
	2	NC	•		
11	1	NO		•	
	2	NC	•		

Note: 1. There are no \rightarrow function for 1NO(10) & 2NO(20)

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Emergency Stop Switch




Application of

RO.8max

Hole Dia Product Appearance Using in nameplates or 42.0 ±0.5 anti-rotation ring or badges .022.3*0,4 Ē 1 TOP Min40.0 $2-2.8_{0}^{+0.2}$ Panel Thickness 0.8mm~12mm 20.5 +0.2 Green

Part Number Explanation



Part Number Table

Description	Part Number	
Non-Illuminated Emergency Stop Switch, 40mm, 1NO, Red	MCC2E-BVE10R	
Non-Illuminated Emergency Stop Switch, 40mm, 1NC, Red	MCC2E-BVE01R	
Non-Illuminated Emergency Stop Switch, 40mm, 2NO, Red	MCC2E-BVE20R	
Non-Illuminated Emergency Stop Switch, 40mm, 2NC, Red	MCC2E-BVE02R	
Non-Illuminated Emergency Stop Switch, 40mm, 1NO+1NC, Red	MCC2E-BVE11R	

Dimensions : Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

