



Digital to Analog +3.5mm Stereo Audio Converter

Please read these instructions carefully before use and retain for future reference.

INTRODUCTION

- This Digital to Analog Audio Converter is designed for either home or professional audio switching.
- It converts Coaxial or Toslink digital audio signals to analog L/R audio and available for connection to an external device such as an amplifier via standard RCA-style jacks and 3.5mm stereo jack, This Converter is small in size and quite easy to install.

FEATURES

This Converter has many features that enable it to perform in a superior manner. Among those features you will find:

- Converts Coaxial or Toslink digital audio signals to analog L/R audio
- Supports sampling rate at 32, 44.1, 48 and 192 KHz.
- 24-bit S/PDIF incoming bit stream on left and right channels
- Provides electromagnetic-noise-free transmission.
- Easy to install and simple to operate.

PACKAGE CONTENTS

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the shipping carton:

- Digital to Analog Audio Converter-----1 PCS
- 5V DC Power Supply-----1 PCS
- User's Manual-----1 PCS

SPECIFICATIONS

Signal Inputs/Output	
Input Audio	Coaxial or Toslink digital audio
Output Audio	R/L +3.5mm audio
Connector	
Input audio connector	Toslink, 1XRCA(Coaxial)
Output audio connector	2XRCA (R/L)
Sampling rate	32, 44.1, 48 and 96 KHz
Mechanical	
Size(LxWxH)	70x60x20mm
Weight (Net)	78g
Warranty	
Limited Warranty	1 Year Parts and Labor
Environmental	
Operating Temperature	0 °C to +70°C
Operating Humidity	10% to 85% RH (no condensation)
Storage Temperature	-10°C to +80°C
Storage Humidity	5% to 90% RH (no condensation)
Power Requirement	
External Power Supply	DC 5V 1A
Power Consumption	0.5 watts (max)
Regulatory Approvals	
Converter Unit	FCC,CE,UL
Power Supply	UL,CE,FCC
Accessories Adapter	
AC Power Adapter	US standard, UK standard and so on
User Manual	English Version

Note: Specifications are subject to change without notice.

PANEL DESCRIPTIONS

Please study the panel drawings below and become familiar with the signal input(s), output(s) and power requirements.



Power: Power Input Status Indicator
 DC 5V: 5V Power Input port
 Toslink: Toslink Digital Audio Input port
 Coaxial: Coaxial Digital Audio Input port
 R/L: R/L Audio Output port
 Audio: Earphone Audio Output port

CONNECTION AND OPERATION

Before installation, please make sure all devices you wish to connect have been turned off.

- Connect the audio source device to the Converter using appropriate Toslink or Coaxial cables.
- Connect the A/V Receivers or Amplifiers to the Converter using appropriate R/L cable.
- The earphone is connected to the converter 3.5mm audio interface.
- Insert the DC side of 5v power supply into the converter and then connect the AC side of the power supply into the wall outlet.

Note: When connected to the Toslink and Coaxial cables at the same time, the product will give priority to Toslink input. Attention: Insert / Extract cable gently.

INSTALLATION AND PRECAUTIONS

- When using electrical appliances basic safety precautions should always be followed.
- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting the PSU to the mains supply.
- Keep the equipment away from moisture or excessive heat.
- There are no user serviceable parts inside.
- Take care when connecting or disconnecting cables.



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.
 When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China, PR2 9PP
 Man Rev 1.0