

9463 Twinax - Blue Hose®

	<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p>
---	---

Description:

78 Ohm twinaxial cable, 20 AWG stranded (7x28) tinned copper, polyethylene insulation, Beldfoil® + tinned copper braid shield 55%, PVC jacket.

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Pairs	1
Total Number of Conductors	2
AWG	20
Stranding	7x28
Conductor Diameter	.038 in.
Conductor Material	TC - Tinned Copper

INSULATION:

Insulation Material	PE - Polyethylene
---------------------	-------------------

PAIR:

Pair Diameter	.154 in.
---------------	----------

Pair Color Code Chart :

Number	Color
1	Clear & Blue

OUTER SHIELD:

Outer Shield Type	Tape/Braid
-------------------	------------

Outer Shield Material :

Layer Number	Material Trade Name	Type	Material	% Coverage (%)
1	Beldfoil®	Tape		100
2		Braid	Tinned Copper	55

OUTER SHIELD DRAIN WIRE :

Outer Shield Drain Wire AWG	20
Outer Shield Drain Wire Stranding	7x28H
Outer Shield Drain Wire Conductor Material	TC - Tinned Copper

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
-----------------------	--------------------------



9463 Twinax - Blue Hose®

OVERALL NOMINAL DIAMETER:

Overall Nominal Diameter	.238 in.
--------------------------	----------

MECHANICAL CHARACTERISTICS:

Operating Temperature Range	-40°C To +80°C
Bulk Cable Weight	36 lbs/1000 ft.
Max. Recommended Pulling Tension	48 lbs.
Min. Bend Radius (Install)	2.5 in.

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CM, CL2
CEC/C(UL) Specification	CM
AWM Specification	Style 2464
PMSHA Specification	SC-182/6
Customer Part Number Reference Specification	Allen Bradley P/N 1770-CD

FLAME TEST:

UL Flame Test	1581 Vertical Tray
---------------	--------------------

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
Plenum Number	89463

ELECTRICAL CHARACTERISTICS:

Nom. Characteristic Impedance	78 Ohms
Nom. Inductance	0.12 µH/ft
Nom. Capacitance Conductor to Conductor @ 1 KHz	19.7 pF/ft
Nom. Cap. Cond. to Other Cond. & Shield @ 1 KHz	36 pF/ft
Nominal Velocity of Propagation	66 %
Nominal Delay	1.54 ns/ft
Nom. Conductor DC Resistance @ 20 Deg. C	9.5 Ohms/1000 ft
Nominal Outer Shield DC Resistance	4.1 Ohms/1000 ft

Nom. Attenuation :

Description	Frequency (MHz)	Start Frequency (MHz)	Stop Frequency (MHz)	Nom. Attenuation (dB/100 ft.)
	1			0.6
	10			2.1
	50			5.0
	100			7.5
	200			11.0
	400			16.0

Max. Operating Voltage - UL	300 V RMS
-----------------------------	-----------



9463 Twinax - Blue Hose®

Other Electrical Characteristic 1 DC Resistance Unbalanced: .77 Ohms/1000 ft Max

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
9463 0011000	78 OHM TWINAX	1000	37	BROWN	
9463 00110000	78 OHM TWINAX	10000	370	BROWN	C
9463 0016000	78 OHM TWINAX	6000	222	BROWN	C Z
9463 0031000	78 OHM TWINAX	1000	37	ORANGE	
9463 00310000	78 OHM TWINAX	10000	370	ORANGE	C Z
9463 0036000	78 OHM TWINAX	6000	222	ORANGE	C Z
9463 0071000	00 OHM TWINAX	1000	37	VIOLET	C
9463 00710000	78 OHM TWINAX	10000	370	VIOLET	C Z
9463 0076000	78 OHM TWINAX	6000	222	VIOLET	C Z
9463 J22100	78 OHM TWINAX	100	4.2	BLUE, STRONG	
9463 J221000	78 OHM TWINAX	1000	37	BLUE, STRONG	C
9463 J22500	78 OHM TWINAX	500	18.5	BLUE, STRONG	
9463 J226000	78 OHM TWINAX	6000	222	BLUE, STRONG	C
9463 J22U1000	78 OHM TWINAX	U1000	37	BLUE, STRONG	
9463 J22U500	78 OHM TWINAX	U500	18.5	BLUE, STRONG	

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 12-20-2002

© 2003 Belden Wire & Cable Company
All Rights Reserved.

Although Belden Electronics Division ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.