




PART NO.

RNBL38-10

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Jagan	28/03/09	Veena	28/03/09	Farnell	13/04/09



Dimensions : Millimetres

Specifications:

Maximum electric current :

AWG	2
Ampere	170

Wire range : 2AWG (38mm²).
 Surface treatment : Tin plated.
 Thickness : 1.80mm.

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2009.

TOLERANCES:
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jagan	28/03/09
CHECKED BY:	DATE:
Veena	28/03/09
APPROVED BY:	DATE:
Farnell	13/04/09

DRAWING TITLE:

Crimp Terminal - Ring

SIZE A	DWG NO.	ELECTRONIC FILE RNBL38-10_DWG	REV A
	M10001999		
SCALE: NTS	U.O.M.: mm	SHEET: 1 OF 2	



PART NO.

RNBL38-10

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Jagan	28/03/09	Veena	28/03/09	Farnell	13/04/09

Specification Table

Description	Material	Part Number
Crimp Terminal, Ring, 10.5mm, PK5	Copper	RNBL38-10

<http://www.farnell.com>

<http://www.newark.com>

<http://www.cpc.co.uk>

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2009.

**TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.**

DRAWN BY:	DATE:
Jagan	28/03/09
CHECKED BY:	DATE:
Veena	28/03/09
APPROVED BY:	DATE:
Farnell	13/04/09

DRAWING TITLE:			
Crimp Terminal - Ring			
SIZE	DWG NO.	ELECTRONIC FILE	REV
A	M10001999	RNBL38-10_DWG	A
SCALE: NTS		U.O.M.: mm	SHEET: 2 OF 2