

KERN 440-35A

The classic balance in the laboratory



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	9 V Block
Charging time:	10 h
Input voltage:	100-240V AC 50/60Hz 0.5A
Mains adapter/adapter included:	EURO CH UK US
Operating time:	20 h
Operating time (Backlight off):	20 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	345 x 215 x 170 mm
Gross weight:	1,380 kg
Net weight:	959 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	165 x 230 x 80 mm
Material weighing plate:	stainless steel
Weighing surface (d):	105

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options:	External calibration
Linearity:	30 mg
Readability [d]:	10 mg
Recommended adjusting weight:	500 g (F2)
Repeatability:	10 mg
Resolution:	60000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	2 h
Weighing capacity [Max]:	600 g
Weighing system:	Strain gauge
Weighing units:	tl (HK) tol g mo lb dwt ct oz tl (Tw) gn ozt

Display

Display digit height (large): 1,500 cm

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	20 mg
Minimum piece weight at piece counting (Normal):	200 mg

Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes