

**HG 2310 LCD**

**Powerful, electronically controlled professional hot air gun with continuously adjustable air flow and temperature control.**

The tremendous power of the HG 2310 LCD makes it suitable for all hot-air jobs. The precision temperature display permits work on materials that respond critically to heat.



1. Visual display of temperature and speed on LCD
2. Selector button for 4 preset programmes
3. Memory button
4. Continuously adjustable temperature
5. Continuously adjustable air flow
6. Non-slip end cap

**Features**

- Sturdy casing for held-held and self-resting use
- Visual display of temperature and speed on LCD
- Four factory-set programmes:



- Double overheating protection: thermostat and thermal cut-out
- Air intake with lattice guard to keep out debris
- Soft grip handle and soft stand for stability

**Settings**

- Continuously adjustable airflow and temperature
- Capability of changing the four preset programmes as required

**HG 2310 LCD**

Prod. No.

**348311**

Dimensions (lxwxh)

260 x 90 x 205 mm

Voltage	230 V / 50 Hz
Output	2300 W
Temperature	stage 1: 50° C stage 2: 50 – 650° C
Display mode	LCD in 10° C steps
Blower	continuously adjustable
Airflow rate	stage 1: 150 – 250 l / min. stage 2: 150 – 500 l / min.
Programmes	factory set 1 = 250° C / approx. 350 l / min. 2 = 350° C / approx. 400 l / min. 3 = 450° C / approx. 500 l / min. 4 = 550° C / approx. 400 l / min.
Memory button	for changing preset programmes
Weight	940 g
	Also available in the sturdy plastic case!



Subject to technical modifications



print  close 