KERN FKB65K0.2



High-resolution bench scale with large weighing range and robust stainless steel weighing plate



Measuring system	
Adjustment options:	External calibration
Linearity:	1 g
Readability [d]:	200 mg
Recommended adjusting weight:	50 kg (E2); 10 kg (E2)
Repeatability:	200 mg
Resolution:	325000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	2 h
Weighing capacity [Max]:	65 kg
Weighing system:	Strain gauge
Weighing units:	g lb dwt oz gn kg ozt

Weighing units:	g lb dwt oz gn kg ozt
Display	
Display digit height (large):	2,500 cm
Counting	
Counting resolution:	325000

323000
200 mg
2 g

Functions	
Conversion function:	yes
Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions	
Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply	
Battery:	6x1.5 V AA
Charging time:	10 h
Input voltage:	100 V - 240V AC 50/60Hz 0.3A
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH AUS UK US
Operating time:	80 h
Operating time (Backlight off):	90 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional - intern

Solvious (optional)		
DAkkS Certificate:	963-129	
Category		
Brand:	KERN	
Category:	Balances	
Product Group:	Bench scale	

Services (optional)

Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 470 x 190 mm
Gross weight:	7,600 kg
Net weight:	6,500 kg
Shipping method:	Parcel service

Construction	
Casing material:	Plastic
Dimensions housing (WxDxH):	350 x 390 x 120 mm
Dimensions of weighing plate (WxDxH):	340 x 240 x 21 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	340 x 240 mm


KERN FKB65K0.2



High-resolution bench scale with large weighing range and robust stainless steel weighing plate

Piktogramme

STANDARD



OPTION



FACTORY

