


KERN PCB 1000-1

The standard in the laboratory



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	9 V Block
Charging time:	8 h
Input voltage:	100-240V AC 50/60Hz 0.5A
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time:	20 h
Operating time (Backlight off):	48 h
Operating time (Backlight on):	24 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	227 x 360 x 175 mm
Gross weight:	1,780 kg
Net weight:	1,270 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	165 x 250 x 79 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Weighing surface (WxD):	130 x 130 mm

Measuring system

Adjustment options:	External calibration
Linearity:	200 mg
Readability [d]:	100 mg
Recommended adjusting weight:	1 kg (M1)
Repeatability:	100 mg
Resolution:	10000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	30 min
Weighing capacity [Max]:	1 kg
Weighing system:	Strain gauge
Weighing units:	tl (HK) tol g mo lb dwt ct oz tl (Tw) kg ozt

Display

Display digit height (large):	2,100 cm
-------------------------------	----------

Counting

Counting resolution:	5000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

Functions

Counting function:	yes
Percentage determination:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes

KERN PCB 1000-1

The standard in the laboratory



Piktogramme

STANDARD



OPTION

