

# KERN PLS4200-2F

High-quality precision scale with comfortable graphic display and enormous weighing range



## Functions

Capacity display:	yes
Counting function:	yes
Density determination function:	yes
Function to save totals:	yes
Percentage determination:	yes
Standby function:	yes
Time display:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

## Power supply

Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH AUS UK US

## Services (optional)

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	500 x 360 x 420 mm
Gross weight:	4,400 kg
Net weight:	3,200 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	210 x 345 x 100 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	210 x 340 x 160 mm
Revolving screw feet:	yes
Weighing surface (d):	160

## Measuring system

Adjustment options:	External calibration
Linearity:	40 mg
Readability [d]:	10 mg
Recommended adjusting weight:	4 kg (E2)
Repeatability:	10 mg
Resolution:	420000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	4 h
Weighing capacity [Max]:	4,200 kg
Weighing system:	Strain gauge
Weighing units:	tl (HK) g mo lb tl (Singap. Malays) dwt ct oz tl (Tw) gn mg ozt

## Display

Display digit height (large):	1,500 cm
Display digit height (small):	4 mm

## Counting

Counting resolution:	84000
Minimum piece weight at piece counting (Laboratory):	50 mg
Minimum piece weight at piece counting (Normal):	500 mg
Reference weight:	yes

# KERN PLS4200-2F



High-quality precision scale with comfortable graphic display and enormous weighing range

## Piktogramme

### STANDARD



### OPTION

