

International  
**IOR** Rectifier

12CWQ06FNPbF

SCHOTTKY RECTIFIER

12 Amp

$$I_{F(AV)} = 12\text{Amp}$$

$$V_R = 60\text{V}$$

#### Major Ratings and Characteristics


| Characteristics                                    | Values     | Units            |
|----------------------------------------------------|------------|------------------|
| $I_{F(AV)}$ Rectangular waveform                   | 12         | A                |
| $V_{RRM}$                                          | 60         | V                |
| $I_{FSM}$ @ tp = 5 $\mu$ s sine                    | 320        | A                |
| $V_F$ @ 6 Apk, $T_J = 125^\circ\text{C}$ (per leg) | 0.57       | V                |
| $T_J$ range                                        | -55 to 150 | $^\circ\text{C}$ |

#### Description/ Features

The 12CWQ06FNPbF surface mount, center tap, Schottky rectifier series has been designed for applications requiring low forward drop and small foot prints on PC board. Typical applications are in disk drives, switching power supplies, converters, free-wheeling diodes, battery charging, and reverse battery protection.

- Popular D-PAK outline
- Center tap configuration
- Small foot print, surface mountable
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Lead-Free ("PbF" suffix)

#### Case Styles



D-PAK (TO-252AA)

# 12CWQ06FNPbF

Bulletin PD-21089 rev. A 05/06

International  
IOR Rectifier

## Voltage Ratings

| Part number                                     | 12CWQ06FNPbF |
|-------------------------------------------------|--------------|
| $V_R$ Max. DC Reverse Voltage (V)               | 60           |
| $V_{RWM}$ Max. Working Peak Reverse Voltage (V) |              |

## Absolute Maximum Ratings

| Parameters                                                                      | 12CWQ...   | Units | Conditions                                                                                                                                                 |
|---------------------------------------------------------------------------------|------------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_{F(AV)}$ Max. Average Forward (Per Leg)<br>Current * See Fig. 5 (Per Device) | 6<br>12    | A     | 50% duty cycle @ $T_C = 131^\circ\text{C}$ , rectangular wave form                                                                                         |
| $I_{FSM}$ Max. Peak One Cycle Non-Repetitive<br>Surge Current * See Fig. 7      | 320<br>105 | A     | 5 $\mu\text{s}$ Sine or 3 $\mu\text{s}$ Rect. pulse<br>10ms Sine or 6ms Rect. pulse<br>Following any rated load condition and with rated $V_{RWM}$ applied |
| $E_{AS}$ Non-Repet. Avalan. Energy (Per Leg)                                    | 7          | mJ    | $T_J = 25^\circ\text{C}$ , $I_{AS} = 1.2$ Amps, $L = 10$ mH                                                                                                |
| $I_{AR}$ Repetitive Avalanche Current (Per Leg)                                 | 0.8        | A     | Current decaying linearly to zero in 1 $\mu\text{sec}$<br>Frequency limited by $T_J$ max. $V_A = 1.5 \times V_R$ typical                                   |

## Electrical Specifications

| Parameters                                                       | 12CWQ... | Units      | Conditions                                                              |
|------------------------------------------------------------------|----------|------------|-------------------------------------------------------------------------|
| $V_{FM}$ Max. Forward Voltage Drop (Per Leg) * See Fig. 1 (1)    | 0.61     | V          | @ 6A<br>$T_J = 25^\circ\text{C}$                                        |
|                                                                  | 0.79     | V          | @ 12A                                                                   |
|                                                                  | 0.57     | V          | @ 6A<br>$T_J = 125^\circ\text{C}$                                       |
|                                                                  | 0.72     | V          | @ 12A                                                                   |
| $I_{RM}$ Max. Reverse Leakage Current (Per Leg) * See Fig. 2 (1) | 3        | mA         | $T_J = 25^\circ\text{C}$                                                |
|                                                                  | 35       | mA         | $T_J = 125^\circ\text{C}$<br>$V_R = \text{rated } V_R$                  |
| $V_{F(TO)}$ Threshold Voltage                                    | 0.36     | V          | $T_J = T_J \text{ max.}$                                                |
| $r_t$ Forward Slope Resistance                                   | 24.14    | m $\Omega$ |                                                                         |
| $C_T$ Typ. Junction Capacitance (Per Leg)                        | 360      | pF         | $V_R = 5V_{DC}$ , (test signal range 100Khz to 1Mhz) $25^\circ\text{C}$ |
| $L_S$ Typical Series Inductance (Per Leg)                        | 5.0      | nH         | Measured lead to lead 5mm from package body                             |

(1) Pulse Width < 300 $\mu\text{s}$ , Duty Cycle <2%

## Thermal-Mechanical Specifications

| Parameters                                                                    | 12CWQ...   | Units              | Conditions                |
|-------------------------------------------------------------------------------|------------|--------------------|---------------------------|
| $T_J$ Max. Junction Temperature Range (*)                                     | -55 to 150 | $^\circ\text{C}$   |                           |
| $T_{stg}$ Max. Storage Temperature Range                                      | -55 to 150 | $^\circ\text{C}$   |                           |
| $R_{thJC}$ Max. Thermal Resistance (Per Leg)<br>Junction to Case (Per Device) | 3.0<br>1.5 | $^\circ\text{C/W}$ | DC operation * See Fig. 4 |
| wt Approximate Weight                                                         | 0.3 (0.01) | g (oz.)            |                           |
| Case Style                                                                    | D-Pak      |                    | Similar to TO-252AA       |
| Marking Device                                                                | 12CWQ06FN  |                    |                           |

(\*)  $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{th(j-a)}}$  thermal runaway condition for a diode on its own heatsink




Fig. 1 - Max. Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)




Fig. 4 - Max. Thermal Impedance  $Z_{thJC}$  Characteristics (Per Leg)




Fig. 5 - Max. Allowable Case Temperature Vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)





Fig. 7 - Max. Non-Repetitive Surge Current (Per Leg)

(2) Formula used:  $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$ ;


$Pd$  = Forward Power Loss =  $I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$  (see Fig. 6);

$Pd_{REV}$  = Inverse Power Loss =  $V_{R1} \times I_{R1} (1 - D)$ ;  $I_{R1} @ V_{R1} = 80\%$  rated  $V_R$


Outline Table



Part Marking Information



## Tape & Reel Information



### Ordering Information Table

**Device Code**

| 12 | C | W | Q | 06 | FN | TRL | PbF |
|----|---|---|---|----|----|-----|-----|
| 1  | 2 | 3 | 4 | 5  | 6  | 7   | 8   |

- 1** - Current Rating (12A)
- 2** - Center Tap Configuration
- 3** - Package Identifier  
W = D-Pak
- 4** - Schottky "Q" Series
- 5** - Voltage Rating (06 = 60V)
- 6** - FN = TO-252AA
- 7** -
  - none = Tube (50 pieces)
  - TR = Tape & Reel
  - TRL = Tape & Reel (Left Oriented)
  - TRR = Tape & Reel (Right Oriented)
- 8** -
  - none = Standard Production
  - PbF = Lead-Free

## 12CWQ06FNPbF

Bulletin PD-21089 rev. A 05/06

International  
**IR** Rectifier

```
12CWQ06FN
*****
* This model has been developed by      *
* Wizard SPICE MODEL GENERATOR (1999)  *
* International Rectifier Corporation)  *
* contains Proprietary Information     *
*****
* SPICE Model Diode is composed by a   *
* simple diode plus paralalled VCG2T   *
*****
.SUBCKT 12CWQ06FN ANO CAT
D1 ANO 1 DMOD (0.03191)
*Define diode model
.MODEL DMOD D(IS=8.95944674613071E-05A,N=1.03666612245428,BV=67V,
+ IBV=0.232083097618696A,RS= 0.00089348,CJO=2.04854724822182E-08,
+ VJ=1.34189135485872,XTI=2, EG=0.732501148466477)
*****
*Implementation of VCG2T
VX 1 2 DC 0V
R1 2 CAT TRES 1E-6
.MODEL TRES RES(R=1,TC1=52.5561105683715)
GP1 ANO CAT VALUE={-ABS(I(VX))*(EXP((( (-3.507402E-03/52.55611)*(V(2,CAT)*1E6)/
(I(VX)+1E-6)-1))+1)*4.963732E-02*ABS(V(ANO,CAT)))-1}
*****
.ENDS 12CWQ06FN

Thermal Model Subcircuit
.SUBCKT 12CWQ06FN 5 1

CTHERM1 5 4 8.75E-04
CTHERM2 4 3 5.33E+01
CTHERM3 3 2 2.05E+02
CTHERM4 2 1 7.61E+02

RTHERM1 5 4 1.00E-07
RTHERM2 4 3 1.65E+00
RTHERM1 3 2 1.12E+00
RTHERM1 2 1 2.29E-01

.ENDS 12CWQ06FN
```

Data and specifications subject to change without notice.  
This product has been designed and qualified for Consumer Level and Lead-Free.  
Qualification Standards can be found on IR's Web site.

International  
**IR** Rectifier

**IR WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7309  
Visit us at [www.irf.com](http://www.irf.com) for sales contact information. 05/06