

# KERN SFB10K1HIP



Stainless steel platform balance with dust and spray protection to IP65 and EC type approval  
[M]



## Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

## Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	20 h

## Services (optional)

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	695 x 415 x 225 mm
Gross weight:	9,780 kg
Net weight:	7,733 kg
Shipping method:	Parcel service
UN number:	2800

## Construction

Cable length of display device:	0 mm
Dimensions of display device (WxDxH):	266 x 165 x 96 mm
Dimensions of weighing plate (WxDxH):	300 x 240 x 105 mm
of stand:	20 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	300 x 400 x 395 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	1 g
Load cell connection:	6-wire
Readability [d]:	1 g
Recommended adjusting weight:	10 kg (M1)
Repeatability:	1 g
Resolution:	10000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-10 kg
Warm up time:	30 min
Weighing capacity [Max]:	10 kg
Weighing system:	Strain gauge
Weighing units:	g lb lb:oz Hj. tJ kg

## Display

Display digit height (large):	5,200 cm
-------------------------------	----------

# KERN SFB10K1HIP



Stainless steel platform balance with dust and spray protection to IP65 and EC type approval [M]

Revolving screw feet: yes

Wall mount: yes

Weighing surface (WxD): 300 x 240 mm

## Piktogramme

### STANDARD



### OPTION



### FACTORY

