


PHE840MX6330MB11R17

Aliases (F840BQ334M275A)

PHE840M/F840, Film, Metallized Polypropylene, Safety, 0.33 uF, 20%, 275 VAC (X2), 760 VDC, 105°C, Lead Spacing = 15mm



Click [here](#) for the 3D model.

Dimensions	
L	18mm MAX
H	16mm MAX
T	8.5mm MAX
S	15mm +/-0.4mm
LL	17mm NOM
F	0.8mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	400

General Information	
Series	PHE840M/F840
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB	No
Performance	No
Notes	Not For New Design, Please Check Possible Alternative Parts (AltPart).

Specifications	
Capacitance	0.33 uF
Capacitance Tolerance	20%
Voltage AC	275 VAC (X2)
Voltage DC	760 VDC
Temperature Range	-55/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.4% 10kHz
Insulation Resistance	30 GOhms
Max dV/dt	100 V/us