

KERN VHB2T1



Pallet truck scale with complete protection against dust and water splashes IP65/67 and a memory for a container weight



DAkkS Certificate: 963-131

Category

Brand:	KERN
Category:	Balances
Product Group:	Pallet truck scale

Packaging & shipping


Delivery:	48 h
Dimensions packaging (WxDxH):	1600 x 560 x 1220 mm
Gross weight:	109 kg
Net weight:	106 kg
Shipping method:	Freight forwarder

Construction

Casing material:	Plastic
Overall dimensions mounted (WxDxH):	1550 x 555 x 1220 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options:	External calibration
Linearity:	2 kg
Readability [d]:	1 kg
Recommended adjusting weight:	1500 kg (M2)
Repeatability:	1 kg
Resolution:	2000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	10 min
Weighing capacity [Max]:	2 t
Weighing system:	Strain gauge
Weighing units:	lb kg

Display

Display digit height (large):	2,800 cm
-------------------------------	----------

Functions

PRE-TARE function:	yes
--------------------	-----

Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Battery:	4x1.5 V AA
Operating time:	80 h

Services (optional)

Adjustment at the location of installation:	961-251
---	---------