

# KERN WTB1K-4N



Ideal for food industry, thanks to its IP65 protection and special checkweighing display, now also with EC type approval [M]



## Power supply

Battery:	no battery
Charging time:	12 h
Input voltage:	110 V - 230 V AC
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	50 h
Operating time (Backlight on):	30 h
Rechargeable battery:	Rchrg. battery optional - intern

## Services (optional)

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

## Category

Brand:	KERN
Category:	Balances

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	340 x 400 x 200 mm
Gross weight:	4 kg
Net weight:	3,200 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	286 x 316 x 126,5 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	286 x 316 x 126,5 mm
Revolving screw feet:	yes
Weighing surface (WxD):	263 x 203 mm

## Piktogramme

### STANDARD



### OPTION



### FACTORY



## Measuring system

Adjustment options:	External calibration
Linearity:	400 mg
Number of weighing ranges:	1
Readability [d]:	200 mg
Recommended adjusting weight:	1,500 kg (M1)
Repeatability:	200 mg
Resolution:	7500
Stabilisation time under laboratory conditions:	2 s
Tare range:	-1,500 kg
Warm up time:	30 min
Weighing capacity [Max]:	1,500 kg
Weighing system:	Strain gauge
Weighing units:	g

## Display

Additional Display possible:	yes
Display digit height (large):	2,500 cm

## Functions

Weighing with tolerance range:	yes
--------------------------------	-----

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %