

Impact wrenches - 1/2" and 3/4"



RP9546



Heavy duty & comfort



FEATURES

- Pin clutch
- Friction ring socket retainer
- Steel clutch housing
- Ergonomic grip
- Forward position: 4 power settings
- Maximum reverse power

BENEFITS

- Good for soft & hard joints
- Withstands rough use
- Operator comfort
- Quick torque adjustment

RP9546 Kits

Same features as RP9546 in kits with Imperial (IKIT) and Metric (MKIT) sockets sizes

See details on page 9



RP9549



Comfort and flexibility

FEATURES

- Single dog clutch
- Friction ring socket retainer
- Steel clutch housing
- Ergonomic grip

BENEFITS

- Good for soft & hard joints
- Withstands rough use
- Versatility & durability

RP9547



Same features as RP9549 with Hole socket retainer



RP9560



Power & durability

FEATURES

- Pin clutch
- Friction ring socket retainer
- High power to weight ratio
- Forward position: 4 power settings
- Maximum reverse power


BENEFITS

- Good for hard joints
- Operator comfort

**RP9551
RP9553
Kits**

Same features as RP9560 in Kits with Imperial (IKIT) and Metric (MKIT) sockets sizes

See details on page 9



RP9561



Strong & durable

FEATURES

- Pin clutch in oil bath
- Hole type socket retainer
- Steel clutch housing
- Built-in power regulator

BENEFITS

- Withstanding rough use
- Ideal for fast rundown with high torque
- Easy for maintenance

See accessories on page 9

MODEL	PART NUMBER	SQUARE DRIVE	FREE SPEED	WORKING TORQUE		MAXIMUM TORQUE		AIR CONSUMPTION		OVERALL LENGTH		NET WEIGHT		NOISE LEVEL	SOUND POWER	VIBRATION	AIR INLET
				Nm	ft lb	Nm	ft lb	l/s	cfm	mm	in.	kg	lb				
RP9546	615 190 9546	1/2	6,400	68-610	50-450	827	625	2.6	5.5	178	7.0	2.49	5.5	95	106	4.9	1/4"
RP9546 MKIT	615 190 0546	1/2	6,400	68-610	50-450	827	625	2.6	5.5	178	7.0	2.49	5.5	95	106	4.9	1/4"
RP9546 IKIT	615 190 8546	1/2	6,400	68-610	50-450	827	625	2.6	5.5	178	7.0	2.49	5.5	95	106	4.9	1/4"
RP9547	615 190 9547	3/4	3,900	271-1017	200-750	1559	1150	18.4	39	226	8.9	5.75	12.6	97	108	8.0	3/8"
RP9549	615 190 9549	3/4	3,900	271-1017	200-750	1559	1150	18.4	39	226	8.9	5.75	12.6	97	108	8.0	3/8"
RP9551 IKIT	615 190 9551	3/4	4,200	200-950	150-700	1360	1000	11.3	24	244	9.6	4.80	10.5	99	110	4.9	3/8"
RP9553 MKIT	615 190 9553	3/4	4,200	200-950	150-700	1360	1000	11.3	24	244	9.6	4.80	10.5	99	110	4.9	3/8"
RP9560	615 190 9560	3/4	4,200	200-950	150-700	1360	1000	11.3	24	244	9.6	4.80	10.5	99	110	4.9	3/8"
RP9561	615 190 9561	3/4	5,500	102-680	75-500	1020	750	14.1	30	216	8.5	4.80	10.5	100	111	5.1	3/8"

@90 PSI(@6.3 Bar) - Listed specifications are for reference only. Please check documents in each tool.