## STAINLESS STEEL FRAME FLOWMETERS

## **FL601G Series**







Optional

- ✓ Heavy-Duty 304 SS Frame, End Plates, and Shield Retainers
- ✓ Full 4.76 mm (¾₁6")

  Thick Polycarbonate
  Safety Shield
- ✓ 316 SS In-Line (Vertical) Fittings
- Detachable, Clear Polycarbonate Scale Plate
- Direct-Reading Scales (GPM Water or SCFM Air)
- Unique Float Stop Design Allows Internals to be Removed and Replaced Without Disturbing Tube or Shield
- ✓ Easy to Clean
- NIST-Traceable Calibration Available
- ✓ Vertical Mount Only

## **SPECIFICATIONS**


Accuracy: ±3% Full Scale Repeatability: ±1% Scale: 127 mm (5")

Wetted Parts: 316 SS, borosilicate

glass, EPR O-Rings

Maximum Temperature: 93°C (200°F)

Connections: FNPT





FL601G shown smaller than actual size.

## Dimensions: mm (inch)

|           |            | · · /     |            |                        |
|-----------|------------|-----------|------------|------------------------|
| С         | D          | Е         | F          | <b>Connection Size</b> |
| 65 (2.6)  | 227 (8.9)  | 64 (2.5)  | 302 (11.9) | ½ FNPT                 |
| 98 (3.9)  | 271 (10.7) | 86 (3.4)  | 343 (13.5) | 1 FNPT                 |
| 137 (5.4) | 298 (11.8) | 135 (5.3) | 406 (16)   | 2 FNPT                 |

| To Order     |                |             |     |            |                 |     |                          |                   |  |  |  |  |
|--------------|----------------|-------------|-----|------------|-----------------|-----|--------------------------|-------------------|--|--|--|--|
| Water Models |                |             |     | Air Models |                 |     |                          |                   |  |  |  |  |
| Model No.    | Maximum<br>GPM | ∆P<br>inH2O | NPT | Model No.  | Maximum<br>SCFM | NPT | Maximum<br>Pressure psig | Weight<br>kg (lb) |  |  |  |  |
| FL601G       | 0.74           | 5           | 1/2 | FL610G     | 3.0             | 1/2 | 250                      | 4.5 (10)          |  |  |  |  |
| FL602G       | 2.00           | 40          | 1/2 | FL611G     | 8.2             | 1/2 | 250                      | 4.5 (10)          |  |  |  |  |
| FL603G       | 5.00           | 14          | 1   | FL612G     | 21.5            | 1   | 200                      | 4.5 (10)          |  |  |  |  |
| FL604P       | 26.00          | 70          | 1   | FL613P     | 90.0            | 1   | 200                      | 4.5 (10)          |  |  |  |  |
| FL605P       | 61.00          | 40          | 2   | FL614P     | 250.0           | 2   | 125                      | 7.7 (17)          |  |  |  |  |
| FL606P       | 116.00         | 45          | 2   | FL615P     | 245.0           | 2   | 125                      | 7.7 (17)          |  |  |  |  |

Comes complete with operator's manual.

For 5-point NIST calibration certificate add suffix "-NIST 5PT" to model number or suffix "-NIST 10PT" for 10-point calibration, for additional cost.

Ordering Examples: FL605P, flowmeter for water with pole-guided float, 61 GPM max flow rate, 2 NPT fitting and 125 psi max pressure. FL611G, flowmeter for air, 8.2 SCFM maximum flow rate, ½ NPT fitting and 250 psig maximum pressure.

<sup>&</sup>quot;G" models have rib-guided floats; "P" models have pole-guided floats. Weights and maximum pressure shown are for both water and air models.