



SAFETY DATA SHEET CONTACT CLEANER C

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME CONTACT CLEANER C
PRODUCT NO. ECCC200DB
APPLICATION Cleaning Product
SUPPLIER ELECTROLUBE. A division of HK
WENTWORTH LTD
KINGSBURY PARK, MIDLAND
ROAD
SWADLINCOTE
DERBYSHIRE, DE11 0AN
UNITED KINGDOM
+44(0)1283 222 111
+44(0)1283 550 177
info@hkw.co.uk
EMERGENCY TELEPHONE +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

2 HAZARDS IDENTIFICATION

Irritating to eyes.

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CLASSIFICATION Xi;R36. R52/53.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
DECAFLUOROPENTANE	420-640-8	138495-42-8	30-60%	R52/53.
PENTAFLUROBUTANE		406-58-6	10-30%	Xi;R36.
ACETONE	200-662-2	67-64-1	1-5%	F;R11 Xi;R36 R66 R67

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION

DO NOT INDUCE VOMITING! Rinse mouth thoroughly.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

CONTACT CLEANER C

SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
ACETONE	WEL	500 ppm	1210 mg/m3	1500 ppm	3620 mg/m3

ENGINEERING MEASURES

No particular ventilation requirements. Provide adequate ventilation. Observe Workplace Exposure Limits and minimise the risk of inhalation of vapours.

RESPIRATORY EQUIPMENT

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid		
COLOUR	Colourless		
ODOUR	Characteristic		
VOLATILITY DESCRIPTION	Volatile.		
SOLUBILITY	Insoluble in water		
RELATIVE DENSITY	1.37 @ 20 °c	VAPOUR PRESSURE	@ °c
AUTO IGNITION TEMPERATURE (°C)	> 750		

10 STABILITY AND REACTIVITY

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalies.

HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Vapours/gases/fumes of: Hydrogen fluoride (HF).

11 TOXICOLOGICAL INFORMATION

CONTACT CLEANER C

GENERAL INFORMATION

No specific health warnings noted.

INHALATION

High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

SKIN CONTACT

Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin. Liquid may irritate skin.

EYE CONTACT

Irritating to eyes.

Other Health Effects

This substance has no evidence of carcinogenic properties.

Name	ACETONE
Toxic Dose 1 - LD 50	5800 mg/kg (oral rat)
Toxic Dose 2 - LD 50	20,000 mg/kg (oral-rbt)
Toxic Conc. - LC 50	76 ppm/4h (inh-rat)
Name	DECAFLUOROPENTANE
Toxic Dose 1 - LD 50	>5000 mg/kg (oral rat)
Toxic Conc. - LC 50	11,100 ppm/4h (inh-rat)
Name	PENTAFLUOROBUTANE
Toxic Dose 1 - LD 50	>2000 mg/kg (oral rat)
Toxic Conc. - LC 50	>200,000 ppm/4h (inh-rat)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

Name	ACETONE
LC 50, 96 Hrs, FISH mg/l	8300
EC 50, 48 Hrs, DAPHNIA, mg/l	12600
Degradability	

The product is easily biodegradable.

Name	DECAFLUOROPENTANE
LC 50, 96 Hrs, FISH mg/l	13.9-27.2
EC 50, 48 Hrs, DAPHNIA, mg/l	11.7
Name	PENTAFLUOROBUTANE
LC 50, 96 Hrs, FISH mg/l	>200
EC 50, 48 Hrs, DAPHNIA, mg/l	>200
IC 50, 72 Hrs, ALGAE, mg/l	113

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION



UK ROAD CLASS	2.2	UK ROAD PACK GR.	Not Applicable
PROPER SHIPPING NAME	AEROSOLS	ADR CLASS	Class 2.2: Non-flammable, non-toxic gases.
UN NO. ROAD	1950		
ADR CLASS NO.	2.2		

CONTACT CLEANER C

ADR PACK GROUP	Not Applicable	ADR LABEL NO.	2.2
CEFIC TEC(R) NO.	20G5A,	RID CLASS NO.	2.2
RID PACK GROUP	Not Applicable	UN NO. SEA	1950
IMDG CLASS	2.2	IMDG PAGE NO.	9022
IMDG PACK GR.	Not Applicable	EMS	F-D; S-U
MARINE POLLUTANT	No.	UN NO. AIR	1950
AIR CLASS	2.2	AIR PACK GR.	Not Applicable

15 REGULATORY INFORMATION

SYMBOLS



Irritant

RISK PHRASES

R36	Irritating to eyes.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

SAFETY PHRASES

S23	Do not breathe vapour/spray.
S25	Avoid contact with eyes.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51	Use only in well-ventilated areas.

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Preparations Directive 1999/45/EC.

Dangerous Substance Directive 67/548/EEC.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

GUIDANCE NOTES

Workplace Exposure Limits EH40. Introduction to Local Exhaust Ventilation HS(G)37. CHIP for everyone HSG(108).

16 OTHER INFORMATION

REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Helen O'Reilly

REVISION DATE JUNE 2008

REV. NO./REPL. SDS GENERATED 2

SDS NO. 11256

CONTACT CLEANER C

RISK PHRASES IN FULL

R11	Highly flammable.
R36	Irritating to eyes.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.