



SAFETY DATA SHEET SPECIALISED CONTACT FLUID

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME SPECIALISED CONTACT FLUID

PRODUCT NO. ESFA55B/01L

APPLICATION Lubricant

SUPPLIER ELECTROLUBE. A division of
HK WENTWORTH LTD
KINGSBURY PARK, MIDLAND
ROAD
SWADLINCOTE
DERBYSHIRE, DE11 0AN
UNITED KINGDOM
+44(0)1283 222 111
+44(0)1283 550 177
info@hkw.co.uk

EMERGENCY TELEPHONE +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

2 HAZARDS IDENTIFICATION

Limited evidence of a carcinogenic effect.

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CLASSIFICATION Carc 3;R40. N;R51/53.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
TETRACHLOROETHYLENE	204-825-9	127-18-4	60-80%	Carc3;R40 N;R51/53

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Perform artificial respiration if breathing has stopped. Keep the affected person warm and at rest. Get prompt medical attention. NOTE! Keep affected person away from heat, sparks and flames!

INGESTION

DO NOT INDUCE VOMITING! NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Remove victim immediately from source of exposure. Provide fresh air, warmth and rest, preferably in comfortable upright sitting position. Rinse mouth thoroughly. Get medical attention.

SKIN CONTACT

Remove affected person from source of contamination. Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

SPECIALISED CONTACT FLUID

EXTINGUISHING MEDIA

Use: Alcohol resistant foam. Powder. Dry chemicals, sand, dolomite etc.

SPECIAL FIRE FIGHTING PROCEDURES

Ventilate closed spaces before entering them. Move container from fire area if it can be done without risk. Use water to keep fire exposed containers cool and disperse vapours. Do not scatter spilled material with more water than needed to fight the fire. Be aware of danger for fire to re-start. Keep run-off water out of sewers and water sources. Dike for water control.

UNUSUAL FIRE & EXPLOSION HAZARDS

May explode in a fire. May develop highly toxic or corrosive fumes if heated. May travel considerable distance to source of ignition and flash back. Vapour explosion and poison hazard indoors, outdoors and in sewers.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Stop leak if possible without risk. Wear necessary protective equipment. Absorb in vermiculite, dry sand or earth and place into containers. Small quantities may be flushed to drains with plenty of water.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level. Risk of vapour concentration on the floor and in low-lying areas. Static electricity and formation of sparks must be prevented.

STORAGE PRECAUTIONS

Flammable/combustible - Keep away from oxidisers, heat and flames. May attack some plastics, rubber and coatings. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

STORAGE CLASS

Flammable liquid storage.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
TETRACHLOROETHYLENE	WEL	50 ppm	345 mg/m ³	100 ppm	689 mg/m ³	

WEL = Workplace Exposure Limit.

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT



ENGINEERING MEASURES

Provide sufficient ventilation during operations which cause vapour formation.

RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit.

HAND PROTECTION

Protective gloves should be used if there is a risk of direct contact or splash. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved safety goggles.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

SPECIALISED CONTACT FLUID

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet.
Wash promptly with soap & water if skin becomes contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid		
COLOUR	Amber		
BOILING POINT (°C)	121	MELTING POINT (°C)	-21
RELATIVE DENSITY	1.305 @ 20 °c	FLASH POINT (°C)	none
AUTO IGNITION TEMPERATURE (°C)	420		

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition.

11 TOXICOLOGICAL INFORMATION

HEALTH WARNINGS

INHALATION. May cause irritation to the respiratory system. SKIN CONTACT. Prolonged or repeated contact leads to drying of skin. May cause skin irritation/eczema. EYE CONTACT. Irritating to eyes. INGESTION. May cause stomach pain or vomiting.

Name	TETRACHLOROETHYLENE
Toxic Conc. - LC 50	4000 ppm/4h (inh-rat)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

No data on possible environmental effects have been found.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION



UK ROAD CLASS	6.1		
PROPER SHIPPING NAME	TETRACHLOROETHYLENE		
UDF Phrase 1	Class 6.1: Toxic Substances		
UN NO. ROAD	1897	UK ROAD PACK GR.	III
ADR CLASS NO.	6.1	ADR CLASS	Class 6.1: Toxic substances.
ADR PACK GROUP	III	HAZARD No. (ADR)	60
ADR LABEL NO.	6.1	HAZCHEM CODE	2Z
CEFIC TEC(R) NO.	61GT1-III	RID CLASS NO.	6.1
RID PACK GROUP	III	UN NO. SEA	1897
IMDG CLASS	6.1	IMDG PACK GR.	III
EMS	F-A; S-A	MFAG	See Guide

SPECIALISED CONTACT FLUID

MARINE POLLUTANT

UN NO. AIR

1897



AIR CLASS

6.1

AIR PACK GR.

III

15 REGULATORY INFORMATION

SYMBOLS



Harmful



Dangerous for the environment

CONTAINS

TETRACHLOROETHYLENE

RISK PHRASES

R40 Limited evidence of a carcinogenic effect.
R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

SAFETY PHRASES

S36/37 Wear suitable protective clothing and gloves.

UK REGULATORY REFERENCES

The Control of Substances Hazardous to Health Regulations 1988.

Chemicals (Hazard Information & Packaging) Regulations.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Helen O'Reilly

REVISION DATE

NOVEMBER 2008

REV. NO./REPL. SDS

3

GENERATED

SDS NO.

11453

RISK PHRASES IN FULL

R40 Limited evidence of a carcinogenic effect.
R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

SPECIALISED CONTACT FLUID

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.