



SAFETY DATA SHEET

SCREEN AND STENCIL SOLVENT

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME SCREEN AND STENCIL SOLVENT

PRODUCT NO. ESSS500ML

SUPPLIER ELECTROLUBE. A division of
HK WENTWORTH LTD
KINGSBURY PARK, MIDLAND
ROAD
SWADLINCOTE
DERBYSHIRE, DE11 0AN
UNITED KINGDOM
+44(0)1283 222 111
+44(0)1283 550 177
info@hkw.co.uk

EMERGENCY TELEPHONE +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

2 HAZARDS IDENTIFICATION

Irritating to eyes.

CLASSIFICATION Xi;R36.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
TETRAHYDROFURFURYL ALCOHOL	202-625-6	97-99-4	60-80%	Xi;R36
1-METHOXY-2-PROPANOL	203-539-1	107-98-2	19.998%	R10

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Perform artificial respiration if breathing has stopped. Keep the affected person warm and at rest. Get prompt medical attention. NOTE! Keep affected person away from heat, sparks and flames!

INGESTION

DO NOT INDUCE VOMITING! NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Remove victim immediately from source of exposure. Provide fresh air, warmth and rest, preferably in comfortable upright sitting position. Rinse mouth thoroughly. Get medical attention.

SKIN CONTACT

Remove affected person from source of contamination. Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

SCREEN AND STENCIL SOLVENT**EXTINGUISHING MEDIA**

Use: Alcohol resistant foam. Powder. Dry chemicals, sand, dolomite etc.

SPECIAL FIRE FIGHTING PROCEDURES

Ventilate closed spaces before entering them. Move container from fire area if it can be done without risk. Use water to keep fire exposed containers cool and disperse vapours. Do not scatter spilled material with more water than needed to fight the fire. Be aware of danger for fire to re-start. Keep run-off water out of sewers and water sources. Dike for water control.

UNUSUAL FIRE & EXPLOSION HAZARDS

May explode in a fire. May develop highly toxic or corrosive fumes if heated. May travel considerable distance to source of ignition and flash back. Vapour explosion and poison hazard indoors, outdoors and in sewers.

6 ACCIDENTAL RELEASE MEASURES**SPILL CLEAN UP METHODS**

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Stop leak if possible without risk.

Wear necessary protective equipment. Absorb in vermiculite, dry sand or earth and place into containers. Small quantities may be flushed to drains with plenty of water.

7 HANDLING AND STORAGE**USAGE PRECAUTIONS**

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level. Risk of vapour concentration on the floor and in low-lying areas. Static electricity and formation of sparks must be prevented.

STORAGE PRECAUTIONS

Flammable/combustible - Keep away from oxidisers, heat and flames. May attack some plastics, rubber and coatings.

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

STORAGE CLASS

Flammable liquid storage.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
1-METHOXY-2-PROPANOL	WEL	100 ppm(Sk)	375 mg/m3(Sk)	150 ppm(Sk)	560 mg/m3(Sk)	

WEL = Workplace Exposure Limit.

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT**ENGINEERING MEASURES**

Provide sufficient ventilation during operations which cause vapour formation.

RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit.

HAND PROTECTION

Protective gloves must be used if there is a risk of direct contact or splash. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved safety goggles.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

SCREEN AND STENCIL SOLVENT

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet.
Wash promptly with soap & water if skin becomes contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid
COLOUR	Colourless
ODOUR	Characteristic
RELATIVE DENSITY	1.025 @ 20 °c

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition.

11 TOXICOLOGICAL INFORMATION

HEALTH WARNINGS

INHALATION. May cause irritation to the respiratory system. SKIN CONTACT. Prolonged or repeated contact leads to drying of skin. May cause skin irritation/eczema. EYE CONTACT. Irritating to eyes. INGESTION. May cause stomach pain or vomiting.

Name	TETRAHYDROFURFURYL ALCOHOL
Toxic Dose 1 - LD 50	25000 mg/kg (oral rat)
Name	1-METHOXY-2-PROPANOL
Toxic Dose 1 - LD 50	5200 mg/kg (oral rat)
Toxic Dose 2 - LD 50	11700 mg/kg (oral-mouse)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

No data on possible environmental effects have been found.

Name	TETRAHYDROFURFURYL ALCOHOL
EC 50, 48 Hrs, DAPHNIA, mg/l	8000
Name	1-METHOXY-2-PROPANOL
LC 50, 96 Hrs, FISH mg/l	20800
EC 50, 48 Hrs, DAPHNIA, mg/l	23300

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION

	No transport warning sign required.		
ROAD TRANSPORT NOTES	Not Classified		
RAIL TRANSPORT NOTES	Not Classified.		
SEA TRANSPORT NOTES	Not Classified.		
AIR TRANSPORT NOTES	Not Classified.		
ADR CLASS	Not classified for transportation.	MARINE POLLUTANT	No.

15 REGULATORY INFORMATION

SYMBOLS

SCREEN AND STENCIL SOLVENT



Irritant

RISK PHRASES

R36 Irritating to eyes.

SAFETY PHRASES

S25 Avoid contact with eyes.

S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

UK REGULATORY REFERENCES

The Control of Substances Hazardous to Health Regulations 1988.

Chemicals (Hazard Information & Packaging) Regulations.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Helen O'Reilly

REVISION DATE

SEPTEMBER 2008

REV. NO./REPL. SDS

4

GENERATED

SDS NO.

10577

RISK PHRASES IN FULL

R10 Flammable.

R36 Irritating to eyes.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.