

#### **TECHNICAL DATA**

# Fluke 730 Series

# Pneumatic/Hydraulic Test Pumps, Filters and Adapters



#### **Features**

- Portable design with 2-year warranty.
- Special surface treatment, scratch and corrosion resistance.
- Fast and steady pressure generation. Multi-stage boosting is used to speed up the process by 5 times.
- Precision shut-off valves to ensure pressure stabilization.
- M20×1.5 female thread quick connection fitting. Test connections can be made without the need for PTFE tape or wrenches.
- Reliable pump design that makes it easy to generate pressure with less time and effort.
- High-resolution fine pressure adjustments.

# **Pneumatic/Hydraulic Test Pumps**

The New Fluke 730 series portable pressure hand pumps feature fast pressure generation, precise control and ease-of-use. These pumps are optimized for pressure stability and consistency during calibration. The high quality design helps to prevent common pressure problems such as plugging, leaking and laborious operation.

Coupled with the Fluke 730G Digital Pressure Calibrator, this complete pressure solution provides an efficient and accurate measurement and calibration of pressure gauges, switches, transmitters, making it ideal for metrology laboratories and industries to use them indoor or outdoor.



#### Fluke-730LTP/40K

- Pressure range -40 kPa to 40 kPa
- Ultra-fine precision adjustment to support low pressure calibration
- Special insulation to reduce the influence of external temperature environment



# Fluke-730LTP/600K

- Pressure range -95kPa to 600kPa
- Pressure is generated by the combination of the pressure rod and screw for faster and smoother pressure increase and decrease
- Safely switch between pressure and vacuum



### Fluke-730PTP/10M

- Pressure range -95 kPa to 10 MPa
- Multi-stage boost system design makes the process 5 times more efficient.
- Safety lock ensures safe switching between positive and negative pressure



### Fluke-730HTP/70M

- Pressure range 0 kPa to 70 MPa
- The screw press design supports high pressure range with less effort.
- Fine pressure adjustment capability with shut-off valve for stable measurements.



# **Specifications**

Model	FLK-730LTP/40K	FLK-730LTP/600K	FLK-730PTP/10M	FLK-730HTP/70M
Pressure range	-40 kPa to 40 kPa	-95 kPa to 600 kPa	-95 kPa to 10 MPa	0 kPa to 70 MPa
Fitting	M20 X 1.5	M20 X 1.5	M20 X 1.5	M20 X 1.5
Weight	2.3 kg	2.9 kg	5.5 kg	5.1 kg
Dimensions (L x W x H)	230 mm x 140 mm x 130 mm	298 mm x 173 mm x 150 mm	360 mm x 250 mm x 145 mm	384 mm x 198 mm x 175 mm
Reservoir volume	2.3 cm3 (0.14 in3)	2.7 cm3 (0.167 in3)	3.5cm3 (0.214 in3)	3.1 cm3 (0.189 in3)
Fine adjustment volume	0.7 cm3 (0.043 in3)	2.1 cm3 (1.281 in3)	2.1cm3 (0.128 in3)	2.1cm3 (0.128 in3)
Pre-pressure volume	42 cm3 (2.563 in3)	14 cm3 (0.854 in3)	49.5 cm3(3.021 in3)	3.8 cm3 (0.232 in3)
Media	Air	Air	Air	Distilled water or mineral oil

# **Optional Adapters and Accessories**

### **FLK-730PFK Pressure Fitting Kit**

38 adapters to meet the requirements of various equipment connection						
M20 x 1.5 M to	1/2" NPT-M	1/2" ZG-M	1/2" G-M	M10 x 1 F	M10 x 1 M	
	3/8" NPT-M	3/8" ZG-M	3/8" G-M	M12 x 1.5 F	M12 x 1.5 M	
	1/4" NPT-M	1/4" ZG-M	1/4" G-M	M14 x 1.5 F	M14 x 1.5 M	
	1/8" NPT-M	1/8" ZG-M	1/8" G-M	M16 x 1.5 F	M16 x 1.5 M	
	1/8" NPT-F	1/8" ZG-F	1/8" G-F	M20 x 1.5 F	M20 x 1.5 M	
	1/4" NPT-F	1/4" ZG-F	1/4" G-F	M20 x 1.5 F, 90°	Ф6 Hose Barb	
	3/8" NPT-F	3/8" ZG-F	3/8" G-F		Ф8 Hose Barb	
	1/2" NPT-F	1/2" ZG-F	1/2" G-F		Ф10 Hose Barb	

#### FLK-730ILF and FLK-730GLSF Filters

FLK-73OILF liquid filters are mainly used in hydraulic (non-corrosive) calibration work to filter a small amount of impurities in the device under test.

FLK-730GLSF liquid-to-gas media separators filters are mainly used in hydraulic (non-corrosive) calibration work to separate and filter a small amount of impurities in the device under test.





Model FLK-730 ILF liquid filter		FLK-730GLSF liquid-to-gas separator	
Pressure range	(O to 70) MPa	(-0.1 to 25) MPa	
Body material	Stainless steel 304		
Filtering fineness	0.05 mm		
External Dimensions	100 mm × φ42 mm	120 mm × φ50 mm	
Weight	0.5 kg	0.6 kg	
Fitting size	Source: M20×1.5 Male thread; Device: M20×1.5 Female thread		



#### **Order information**

FLUKE 730 series Test Pump

#### Included

- 20 qty of seals for M20 x 1.5 quick-connection
- 2 qty of M20 plug connectors to prevent contamination

Model	Description
FLK-730LTP/40K	LOW PRESSURE TEST PUMP40 TO 40 kPa, -5.8 TO 5.8 PSI
FLK-730LTP/600K	LOW PRESSURE TEST PUMP95 TO 600 kPa, -13.8 TO 87 PSI
FLK-730PTP/10M	PNEUMATIC TEST PUMP0.095 TO 10 MPa, -13.8 TO 1451 PSI
FLK-730HTP/70M	HYDRAULIC TEST PUMP. O TO 70 MPa, O TO 10153 PSI
FLK-730PFK	PRESSURE FITTING KIT
FLK-730GLSF	GAS AND LIQUID SEPARATION FILTER
FLK-730ILF	IN-LINE LIQUID FILTER

Visit www.fluke.com to get complete details on these products or ask your local Fluke sales representative.

Fluke. Keeping your world up and running.®

#### Fluke South East Asia Pte Ltd

1 Clementi Loop, #06-02/03/04, Singapore 129808

Tel: (65)6799-5575 | Fax: (65)6799-5577 Email: fsea.info@fluke.com Web access: www.fluke.com.sg

© 2021 Fluke Corporation. 3/2021 specifications subject to change without notice. 20210301rev-en