

Product Overview

FAN251015: 15A Synchronous Buck Regulator with PMBUS

For complete documentation, see the data sheet.

The FAN251015 is a highly efficient synchronous buck regulator with digital interface, capable of operating with an input range from 4.5 V to 18 V and supporting up to 15 A load currents. The FAN2510xx utilizes a fixed− frequency voltage− mode control architecture to provide a synchronized constant switching frequency while ensuring fast transient response. Switching frequency and over− current protection can be programmed to provide a flexible solution for various applications. Output over− voltage, under− voltage, over− current, and thermal shutdown protections help prevent damage to the device during fault conditions.

Features

• PMBUS 1.3.1 Compatible

VIN Range: 4.5 V to 18 V

· Accurate Voltage, Current and Thermal Telemetry Reporting

High Efficiency: Over 96% Peak
Continuous Output Current: 15 A
Internal Linear Bias Regulator

Internal Linear Bias Regulator

• Precision Reference: ±0.7% Over Temperature

Output Voltage Range: 0.5 V to 5.5 V
Adjustable Frequency: 200 kHz to 2.2 MHz

Programmable Soft-Start

For more features, see the data sheet

Applications

· Point of Load

· ASIC, CPU Core and I/O Supplies

Benefits

Telemetry reporting, custom configuration, fault recording/reading with NVM

End Products

- · Server and Desktop Computers, Notebooks, Gaming
- · Telecommunications
- · High Density Power Solutions

Part Electrical Specifications												
Product	Pricing (\$/Unit)	Compliance	Status	Topology	Control Mode	V _{CC} Min (V)	V _{CC} Max (V)	V _o Typ (V)	I _o Typ (A)	Efficienc y (%)	f _{sw} Typ (kHz)	Package Type
FAN251015MNTXG	2	Pb-free Halide free non AEC-Q and PPAP	NEW	Step- Down	Voltage Mode	4.5	18	0.5V to 5.5V	Up to 15A	96% Peak	200kHz to 2.2Mhz	WQFN- 34

For more information please contact your local sales support at www.onsemi.com.

Created on: 8/5/2021